

Specification Sheet

Part Number: 110-70089



Calibration Tool, 1/pkg

Article Number	110-70089
Type	EVO Calibration Tool
Color	Various (MIX)
Features & Benefits	<ul style="list-style-type: none">•Advanced TLC technology provides operational reliability and durability resulting in fewer repairs and an extended lifespan.•Lightweight tool with the most technologically advanced ergonomic design for reducing work-related risks such as fatigue and injury that effect productivity.•Tension dial offers 33 precise, easy-to-read settings (with 1/4" increments) that reduce subjectivity or the need for fine tuning.•Tension lock-in mechanism prevents operator from changing tension setting during critical applications.
Quantity Per	EA

Product Description

HellermannTyton's EVO7 mechanical hand tool was ergonomically designed to reduce the risks of repetitive stress injuries to operators while concurrently increasing productivity. The EVO 7 Tension/Lock/Cut Technology delivers performance, safety and comfort for the operators. Available in a standard grip span (EVO 7) or short grip span (EVO 7SP), for smaller hands. Additional accessories are available.

Short Description	Calibration Tool, 1/pkg
Global Part Name	EVO Calibration Tool-MIX
Technical Description	Calibration tool to be used for removal of cap at back of tension knob and for calibrating tool on site
Tension Setting Tools	Adjustable
Reach Complaint(Article 33)	Yes
ROHS Complaint	Yes
Package Quantity(Imperial)	1
Package Quantity (Metric)	1
Customs Number	8205599000
Content Unit(BMEcat)	pcs.