

Specification Sheet

Part Number: 110-70133

Product Image EVO 7 and/or EVO 7SP Nose Piece, 3mm tail, 1/pkg

Article Number	110-70133
Type	SP EVO7 NOSEPIECE 3MM
Color	Various (MIX)
Features & Benefits	<ul style="list-style-type: none">•Advanced TLC technology provides operational reliability and durability resulting in fewer repairs and an extended lifespan.•Lightweight tool with the most technologically advanced ergonomic design for reducing work-related risks such as fatigue and injury that effect productivity.•Tension dial offers 33 precise, easy-to-read settings (with ¼" increments) that reduce subjectivity or the need for fine tuning.•Tension lock-in mechanism prevents operator from changing tension setting during critical applications.
Quantity Per	bag
Product Description	HellermannTyton's EVO 7 mechanical hand tool is ergonomically designed to reduce the risks of repetitive stress injuries to operators while simultaneously increasing productivity. The EVO 7 Tension/Lock/Cut Technology delivers performance, safety and comfort for operators. Available in a standard grip span (EVO 7) or short grip span (EVO 7SP) for smaller hands. Additional accessories are available.
Short Description	EVO 7 and/or EVO 7SP Nose Piece, 3mm tail, 1/pkg
Global Part Name	SP EVO7 NOSEPIECE 3MM-MIX
Tension Setting Tools	Adjustable

Reach Complaint(Article 33)	Yes
ROHS Complaint	Yes
Package Quantity(Imperial)	1
Package Quantity (Metric)	1
Customs Number	8205599000
Content Unit(BMEcat)	pcs.
Weight (Metric)	0.008
Weight (Imperial)	0.017