

## Specification Sheet

Part Number: T50L0M4



Cable Tie, 15.35" Long, UL Rated, 50lb Tensile Strength, PA66, Black, 1000/pkg

Article Number	111-00504
Type	T50L
Color	Black (BK)
Features & Benefits	<ul style="list-style-type: none"><li>•Engineered and manufactured for maximum performance and quality.</li><li>•Made from 100% high-quality plastic to ensure efficient recycling.</li><li>•Inside serration for a strong grip onto bundles.</li><li>•Easy application either manually or with a tensioning tool.</li><li>•Bent tail allows for simpler insertion.</li></ul>
Quantity Per	bag

### Product Description

T-Series Cable Ties feature inside serrations to provide a positive hold on wire and cable bundles. The head design guarantees high tensile strength and a low insertion force. The bent tail design allows quick and simple installations by hand. For high-volume applications, tensioning tools are available to ensure consistent and safe installation.

**Short Description**

Cable Tie, 15.35" Long, UL Rated, 50lb Tensile Strength, PA66, Black, 1000/pkg

**Global Part Name**

T50L-PA66-BK

**Minimum Tensile Strength (Imperial)**

50.0

**Minimum Tensile Strength (Metric)**

225.0

**Length L (Imperial)**

15.35

**Length L (Metric)**

389.89

**Identification Plate Position**

none

**Releasable Closure**

No

**Tie Closure**

plastic pawl

**Variant**

Inside Serrated

**Width W (Imperial)**

0.19

**Width W (Metric)**

4.8

**Bundle Diameter Min (Imperial)**

0.06

**Bundle Diameter Min (Metric)**

1.5

**Bundle Diameter Max (Imperial)**

4.3

**Bundle Diameter Max (Metric)**

109.2

<b>Thickness T (Metric)</b>	1.4
<b>Material</b>	Polyamide 6.6 (PA66)
<b>Material Shortcut</b>	PA66
<b>Flammability</b>	UL 94 V2
<b>Halogen free</b>	Yes
<b>Operating Temperature (Metric)</b>	-40°F to +185°F (-40°C to +85°C)
<b>ROHS Complaint</b>	Yes
<b>Certification/Specification WEB</b>	UL-ZODZ2.E64139
<b>UL Recognized (US)</b>	Yes
<b>UL Listed (US and Canada)</b>	Yes
<b>UL Recognized (US and Canada)</b>	Yes
<b>UL Listed (US)</b>	Yes
<b>Package Quantity(Imperial)</b>	1000
<b>Package Quantity (Metric)</b>	1000
<b>Customs Number</b>	3926909988

---

© 2019 HellermannTyton. All Rights Reserved.

[Contact Us](#) [RoHS/WEEE Compliance](#) [Disclaimer](#) [Terms and Conditions](#)