

Specification Sheet

Part Number: T18R6M4



Cable Tie, 4" Long, UL Rated, 18lb Tensile Strength, PA66, Blue, 1000/pkg

Article Number	111-01845
Type	T18R
Color	Blue (BU)
Features & Benefits	<ul style="list-style-type: none">• Inside serrations allow for strong grip on cables and wire bundles.• Head design provides high tensile strength with very low insertion force.• Bent tail ensures a quick and simple installation.
Quantity Per	bag
Product Description	T-Series Cable Ties feature inside serrations to provide a positive hold on wire and cable bundles. The head design guarantees high tensile strength and a low insertion force. The bent tail design allows quick and simple installations by hand. For high-volume applications, tensioning tools are available to ensure consistent and safe installation.
Short Description	Cable Tie, 4" Long, UL Rated, 18lb Tensile Strength, PA66, Blue, 1000/pkg

Global Part Name

T18R-PA66-BU

Minimum Tensile Strength (Imperial)

18.0

Minimum Tensile Strength (Metric)

80.0

Length L (Imperial)

4.0

Length L (Metric)

101.6

Identification Plate Position

none

Releasable Closure

No

Tie Closure

plastic pawl

Variant

Inside Serrated

Width W (Imperial)

0.10

Width W (Metric)

2.5

Bundle Diameter Min (Imperial)

0.06

Bundle Diameter Min (Metric)

1.5

Bundle Diameter Max (Imperial)

0.87

Bundle Diameter Max (Metric)

22.0

Thickness T (Metric)

1.0

Height H (Metric)

3.7

Material	Polyamide 6.6 (PA66)
-----------------	----------------------

Material Shortcut	PA66
--------------------------	------

US MIL SPEC	MS3367-4-6
--------------------	------------

SAE-AS33671	Flammability
-------------	---------------------

UL 94 V2	Halogen free
----------	---------------------

Yes	Operating Temperature (Metric)
-----	---------------------------------------

-40°F to +185°F (-40°C to +85°C)	ROHS Complaint
----------------------------------	-----------------------

Yes	Certification/Specification WEB
-----	--

CAGE Code 53421	UL Recognized (US)
-----------------	---------------------------

Yes	UL Listed (US and Canada)
-----	----------------------------------

Yes	UL Recognized (US and Canada)
-----	--------------------------------------

Yes	UL Listed (US)
-----	-----------------------

Yes	
-----	--

Package Quantity(Imperial)	1000
-----------------------------------	------

Package Quantity (Metric)	1000
----------------------------------	------

Customs Number

3926909988

© 2019 HellermannTyton. All Rights Reserved.

[Contact Us](#) [RoHS/WEEE Compliance](#) [Disclaimer](#) [Terms and Conditions](#)