

Specification Sheet

Part Number: T18I9VOM4



Flame-Retardant Cable Tie, 5.5" Long, UL Rated, 18lb Tensile Strength, PA66V0, Natural, 1000/pkg

Article Number	111-02304
Type	T18I
Color	Natural (NA)
Features & Benefits	<ul style="list-style-type: none">•Feature a UL 94 V-0 rating to comply with low flame and smoke requirements.•Inside serrations provide strong grip on cables and wire bundles.•Easy application either manually or with a tensioning tool.•Bent tail ensures a quick and simple installation.
Quantity Per	bag

Product Description

HellermannTyton's flame retardant cable ties meet the UL 94 V-0 flammability requirements. T-Series Cable Ties feature inside serrations to provide a positive hold on wire and cable bundles. The head design guarantees high tensile strength and a low insertion force. The bent tail design allows quick and simple installations by hand. For high-volume applications, tensioning tools are available to ensure consistent and safe installation.

Short Description

Flame-Retardant Cable Tie, 5.5" Long, UL Rated, 18lb Tensile Strength, PA66V0, Natural, 1000/pkg

Global Part Name

T18I-PA66V0-NA

Minimum Tensile Strength (Imperial)

18.0

Minimum Tensile Strength (Metric)

80.0

Length L (Imperial)

5.5

Length L (Metric)

139.7

Identification Plate Position

none

Releasable Closure

No

Tie Closure

plastic pawl

Variant

Inside Serrated

Width W (Imperial)

0.10

Width W (Metric)

2.5

Bundle Diameter Min (Imperial)

0.12

Bundle Diameter Min (Metric)

3.0

Bundle Diameter Max (Imperial)

1.38

Bundle Diameter Max (Metric)

35.0

Material	Polyamide 6.6 V0 (PA66V0)
Material Shortcut	PA66V0
Flammability	UL 94 V0
Halogen free	Yes
Operating Temperature (Metric)	-40°F to +185°F (-40°C to +85°C)
ROHS Complaint	Yes
UL Recognized (US)	Yes
UL Recognized (US and Canada)	Yes
Package Quantity(Imperial)	1000
Package Quantity (Metric)	1000
Customs Number	3926909988