

## Specification Sheet

Part Number: T18I9M4



Cable Tie, 5.5" Long, UL Rated, 18lb Tensile Strength, PA66, Natural, 1000/pkg

Article Number	111-02322
Type	T18I
Color	Natural (NA)
Features & Benefits	<ul style="list-style-type: none"><li>• Inside serrations allow for strong grip on cables and wire bundles.</li><li>• Head design provides high tensile strength with very low insertion force.</li><li>• Bent tail ensures a quick and simple installation.</li></ul>
Quantity Per	bag

### Product Description

T-Series Cable Ties feature inside serrations to provide a positive hold on wire and cable bundles. The head design guarantees high tensile strength and a low insertion force. The bent tail design allows quick and simple installations by hand. For high-volume applications, tensioning tools are available to ensure consistent and safe installation.

**Short Description**

Cable Tie, 5.5" Long, UL Rated, 18lb Tensile Strength, PA66, Natural, 1000/pkg

**Global Part Name**

T18I-PA66-NA

**Minimum Tensile Strength (Imperial)**

18.0

**Minimum Tensile Strength (Metric)**

80.0

**Length L (Imperial)**

5.5

**Length L (Metric)**

139.7

**Identification Plate Position**

none

**Releasable Closure**

No

**Tie Closure**

plastic pawl

**Variant**

Inside Serrated

**Width W (Imperial)**

0.10

**Width W (Metric)**

2.5

**Bundle Diameter Min (Imperial)**

0.06

**Bundle Diameter Min (Metric)**

1.5

**Bundle Diameter Max (Imperial)**

1.38

**Bundle Diameter Max (Metric)**

35.0

<b>Material</b>	Polyamide 6.6 (PA66)
<b>Material Shortcut</b>	PA66
<b>Flammability</b>	UL 94 V2
<b>Halogen free</b>	Yes
<b>Operating Temperature (Metric)</b>	-40°F to +185°F (-40°C to +85°C)
<b>Reach Complaint(Article 33)</b>	Yes
<b>ROHS Complaint</b>	Yes
<b>Certification/Specification WEB</b>	DNV GL   IEC 62275:2006
<b>UL Recognized (US)</b>	Yes
<b>UL Listed (US and Canada)</b>	Yes
<b>UL Recognized (US and Canada)</b>	Yes
<b>UL Listed (US)</b>	Yes
<b>Package Quantity(Imperial)</b>	1000
<b>Package Quantity (Metric)</b>	1000
<b>Customs Number</b>	3926909988

