

Specification Sheet

Part Number: T30XL0M4



Article Number

111-02903

Type

T30XL

Color

Black (BK)

Features & Benefits

- Inside serrations allow for strong grip on cables and wire bundles.
- Head design provides high tensile strength with very low insertion force.
- Bent tail ensures a quick and simple installation.

Quantity Per

bag

Product Description

T-Series Cable Ties feature inside serrations to provide a positive hold on wire and cable bundles. The head design guarantees high tensile strength and a low insertion force. The bent tail design allows quick and simple installations by hand. For high-volume applications, tensioning tools are available to ensure consistent and safe installation.

Short Description

Cable Tie, 14" Long, UL Rated, 30lb Tensile Strength, PA66, Black, 1000/pkg

Global Part Name

T30XL-PA66-BK

Minimum Tensile Strength (Imperial)

30.0

Minimum Tensile Strength (Metric)

135.0

Length L (Imperial)

14.0

Length L (Metric)

355.0

Identification Plate Position

none

Releasable Closure

No

Tie Closure

plastic pawl

Variant

Inside Serrated

Width W (Imperial)

0.14

Width W (Metric)

3.6

Bundle Diameter Min (Imperial)

0.06

Bundle Diameter Min (Metric)

1.5

Bundle Diameter Max (Imperial)

4.13

Bundle Diameter Max (Metric)

104.9

| | |
|---------------------------------------|----------------------------------|
| Material | Polyamide 6.6 (PA66) |
| Material Shortcut | PA66 |
| Flammability | UL 94 V2 |
| Halogen free | Yes |
| Operating Temperature (Metric) | -40°F to +185°F (-40°C to +85°C) |
| Reach Complaint(Article 33) | Yes |
| ROHS Complaint | Yes |
| UL Recognized (US) | Yes |
| UL Listed (US and Canada) | Yes |
| UL Recognized (US and Canada) | Yes |
| Package Quantity(Imperial) | 1000 |
| Package Quantity (Metric) | 1000 |
| Customs Number | 3926909988 |
| Content Unit(BMEcat) | pcs. |

