

Specification Sheet

Part Number: T30R6M4



Cable Tie, 5.8" Long, UL Rated, 30lb Tensile Strength, PA66, Blue, 1000/pkg

Article Number	111-03036
Type	T30R
Color	Blue (BU)
Features & Benefits	<ul style="list-style-type: none">• Inside serrations allow for strong grip on cables and wire bundles.• Head design provides high tensile strength with very low insertion force.• Bent tail ensures a quick and simple installation.
Quantity Per	bag
Product Description	T-Series Cable Ties feature inside serrations to provide a positive hold on wire and cable bundles. The head design guarantees high tensile strength and a low insertion force. The bent tail design allows quick and simple installations by hand. For high-volume applications, tensioning tools are available to ensure consistent and safe installation.
Short Description	Cable Tie, 5.8" Long, UL Rated, 30lb Tensile Strength, PA66, Blue, 1000/pkg

Global Part Name

T30R-PA66-BU

Minimum Tensile Strength (Imperial)

30.0

Minimum Tensile Strength (Metric)

135.0

Length L (Imperial)

5.8

Length L (Metric)

147.32

Identification Plate Position

none

Releasable Closure

No

Tie Closure

plastic pawl

Variant

Inside Serrated

Width W (Imperial)

0.14

Width W (Metric)

3.6

Bundle Diameter Min (Imperial)

0.06

Bundle Diameter Min (Metric)

1.5

Bundle Diameter Max (Imperial)

1.38

Bundle Diameter Max (Metric)

35.0

Thickness T (Metric)

1.1

Material	Polyamide 6.6 (PA66)
-----------------	----------------------

Material Shortcut	PA66
--------------------------	------

US MIL SPEC	MS3367-5-6
--------------------	------------

SAE-AS33671

Flammability

UL 94 V2

Halogen free

Yes

Operating Temperature (Metric)

-40°F to +185°F (-40°C to +85°C)

ROHS Complaint

Yes

Certification/Specification WEB

UL-ZODZ.E64139 CAGE Code 53421

UL Recognized (US)

Yes

UL Listed (US and Canada)

Yes

UL Recognized (US and Canada)

Yes

UL Listed (US)

Yes

Package Quantity(Imperial)	1000
-----------------------------------	------

Package Quantity (Metric)	1000
----------------------------------	------

Customs Number	3926909988
-----------------------	------------

Weight (Metric)

0.7

© 2019 HellermannTyton. All Rights Reserved.

[Contact Us](#) [RoHS/WEEE Compliance](#) [Disclaimer](#) [Terms and Conditions](#)