

## Specification Sheet

Part Number: T30R0VOC2



Flame-Retardant Cable Tie, 5.8" Long, UL Rated, 30lb Tensile Strength, PA66V0, Black, 100/pkg

Article Number	111-03072
Type	T30R
Color	Black (BK)
Features & Benefits	<ul style="list-style-type: none"><li>•Feature a UL 94 V-0 rating to comply with low flame and smoke requirements.</li><li>•Inside serrations provide strong grip on cables and wire bundles.</li><li>•Easy application either manually or with a tensioning tool.</li><li>•Bent tail ensures a quick and simple installation.</li></ul>
Quantity Per	bag

### Product Description

HellermannTyton's flame retardant cable ties meet the UL 94 V-0 flammability requirements. T-Series Cable Ties feature inside serrations to provide a positive hold on wire and cable bundles. The head design guarantees high tensile strength and a low insertion force. The bent tail design allows quick and simple installations by hand. For high-volume applications, tensioning tools are available to ensure consistent and safe installation.

<b>Short Description</b>	Flame-Retardant Cable Tie, 5.8" Long, UL Rated, 30lb Tensile Strength, PA66V0, Black, 100/pkg
<b>Global Part Name</b>	T30R-PA66V0-BK
<b>Minimum Tensile Strength (Imperial)</b>	30.0
<b>Minimum Tensile Strength (Metric)</b>	135.0
<b>Length L (Imperial)</b>	6.0
<b>Length L (Metric)</b>	150.0
<b>Identification Plate Position</b>	none
<b>Releasable Closure</b>	No
<b>Tie Closure</b>	plastic pawl
<b>Variant</b>	Inside Serrated
<b>Width W (Imperial)</b>	0.14
<b>Width W (Metric)</b>	3.6
<b>Bundle Diameter Min (Imperial)</b>	0.12
<b>Bundle Diameter Min (Metric)</b>	3.0
<b>Bundle Diameter Max (Imperial)</b>	1.38
<b>Bundle Diameter Max (Metric)</b>	35.0

<b>Thickness T (Metric)</b>	1.1
<b>Material</b>	Polyamide 6.6 V0 (PA66V0)
<b>Material Shortcut</b>	PA66V0
<b>Flammability</b>	UL 94 V0
<b>Operating Temperature (Metric)</b>	-40°F to +185°F (-40°C to +85°C)
<b>ROHS Complaint</b>	Yes
<b>Certification/Specification WEB</b>	UL-ZODZ2.E64139
<b>UL Recognized (US)</b>	Yes
<b>UL Recognized (US and Canada)</b>	Yes
<b>Package Quantity(Imperial)</b>	100
<b>Package Quantity (Metric)</b>	100
<b>Customs Number</b>	3926909988

