

Specification Sheet

Part Number: T30L0C2



Article Number

111-03313

Type

T30L

Color

Black (BK)

Features & Benefits

- Inside serrations allow for strong grip on cables and wire bundles.
- Head design provides high tensile strength with very low insertion force.
- Bent tail ensures a quick and simple installation.

Quantity Per

bag

Product Description

T-Series Cable Ties feature inside serrations to provide a positive hold on wire and cable bundles. The head design guarantees high tensile strength and a low insertion force. The bent tail design allows quick and simple installations by hand. For high-volume applications, tensioning tools are available to ensure consistent and safe installation.

Short Description

Cable Tie, 7.8" Long, UL Rated, 30lb Tensile Strength, PA66, Black, 100/pkg

Global Part Name

T30L-PA66-BK

Minimum Tensile Strength (Imperial)

30.0

Minimum Tensile Strength (Metric)

135.0

Length L (Imperial)

7.8

Length L (Metric)

198.0

Identification Plate Position

none

Releasable Closure

No

Tie Closure

plastic pawl

Variant

Inside Serrated

Width W (Imperial)

0.14

Width W (Metric)

3.6

Bundle Diameter Min (Imperial)

0.06

Bundle Diameter Min (Metric)

1.5

Bundle Diameter Max (Imperial)

1.97

Bundle Diameter Max (Metric)

50.0

Material	Polyamide 6.6 (PA66)
Material Shortcut	PA66
Flammability	UL 94 V2
Halogen free	Yes
Operating Temperature (Metric)	-40°F to +185°F (-40°C to +85°C)
ROHS Complaint	Yes
UL Recognized (US)	Yes
UL Listed (US and Canada)	Yes
UL Recognized (US and Canada)	Yes
Package Quantity(Imperial)	100
Package Quantity (Metric)	100
Customs Number	3926909988