

## Specification Sheet

Part Number: T30L9C2



Cable Tie, 7.8" Long, UL Rated, 30lb Tensile Strength, PA66, Natural, 100/pkg

<b>Article Number</b>	111-03325
<b>Type</b>	T30L
<b>Color</b>	Natural (NA)
<b>Features &amp; Benefits</b>	<ul style="list-style-type: none"><li>• Inside serrations allow for strong grip on cables and wire bundles.</li><li>• Head design provides high tensile strength with very low insertion force.</li><li>• Bent tail ensures a quick and simple installation.</li></ul>
<b>Quantity Per</b>	bag
<b>Product Description</b>	T-Series Cable Ties feature inside serrations to provide a positive hold on wire and cable bundles. The head design guarantees high tensile strength and a low insertion force. The bent tail design allows quick and simple installations by hand. For high-volume applications, tensioning tools are available to ensure consistent and safe installation.
<b>Short Description</b>	Cable Tie, 7.8" Long, UL Rated, 30lb Tensile Strength, PA66, Natural, 100/pkg

Global Part Name

T30L-PA66-NA

Minimum Tensile Strength (Imperial)

30.0

Minimum Tensile Strength (Metric)

135.0

Length L (Imperial)

7.8

Length L (Metric)

198.0

Identification Plate Position

none

Releasable Closure

No

Tie Closure

plastic pawl

Variant

Inside Serrated

Width W (Imperial)

0.14

Width W (Metric)

3.6

Bundle Diameter Min (Imperial)

0.06

Bundle Diameter Min (Metric)

1.5

Bundle Diameter Max (Imperial)

1.97

Bundle Diameter Max (Metric)

50.0

<b>Material</b>	Polyamide 6.6 (PA66)
<b>Material Shortcut</b>	PA66
<b>Flammability</b>	UL 94 V2
<b>Halogen free</b>	Yes
<b>Operating Temperature (Metric)</b>	-40°F to +185°F (-40°C to +85°C)
<b>ROHS Complaint</b>	Yes
<b>UL Recognized (US)</b>	Yes
<b>UL Listed (US and Canada)</b>	Yes
<b>UL Recognized (US and Canada)</b>	Yes
<b>UL Listed (US)</b>	Yes
<b>Package Quantity(Imperial)</b>	100
<b>Package Quantity (Metric)</b>	100
<b>Customs Number</b>	3926909988