

Specification Sheet

Part Number: T30L0HSM4



High-Temp Cable Tie, 7.8" Long, UL Rated, 30lb Tensile Strength, PA66HS, Black, 1000/pkg

Article Number	111-03341
Type	T30L
Color	Black (BK)
Features & Benefits	<ul style="list-style-type: none">• Heat stabilized cable ties provide excellent resistance to high heat exposures.• Inside serrations allow for strong grip on cables and wire bundles.• Head design provides high tensile strength with very low insertion force.• Bent tail ensures a quick and simple installation.
Quantity Per	bag

Product Description

HellermannTyton high temperature cable ties are made of specially formulated materials providing various levels of temperature resistance and performance. The cable ties feature inside serrations providing a positive hold onto wire and cable bundles. The head design guarantees high tensile strength, as well as a low insertion force. The bent tail design allows quick and simple installations by hand. For high volume applications, tensioning tools are available to ensure consistent and safe installation.

Short Description	High-Temp Cable Tie, 7.8" Long, UL Rated, 30lb Tensile Strength, PA66HS, Black, 1000/pkg
Global Part Name	T30L-PA66HS-BK
Minimum Tensile Strength (Imperial)	30.0
Minimum Tensile Strength (Metric)	135.0
Length L (Imperial)	7.8
Length L (Metric)	198.0
Identification Plate Position	none
Releasable Closure	No
Tie Closure	plastic pawl
Variant	Inside Serrated
Width W (Imperial)	0.14
Width W (Metric)	3.6
Bundle Diameter Min (Imperial)	0.06
Bundle Diameter Min (Metric)	1.5
Bundle Diameter Max (Imperial)	2.0
Bundle Diameter Max (Metric)	50.8

Material	Polyamide 6.6 heat stabilized (PA66HS)
Material Shortcut	PA66HS
Flammability	UL 94 V2
Halogen free	Yes
Operating Temperature (Metric)	-40°F to +257°F (-40°C to +125°C)
ROHS Complaint	Yes
Certification/Specification WEB	UL-ZODZ2.E64139 VG U48/04103
UL Recognized (US)	Yes
UL Listed (US and Canada)	Yes
UL Recognized (US and Canada)	Yes
UL Listed (US)	Yes
Package Quantity(Imperial)	1000
Package Quantity (Metric)	1000
Customs Number	3926909988

