

## Specification Sheet

Part Number: T40R9M4



Cable Tie, 8.3" Long, UL Rated, 40lb Tensile Strength, PA66, Natural, 1000/pkg

Article Number	111-04131
Type	T40R(U)
Color	Natural (NA)
Features & Benefits	<ul style="list-style-type: none"><li>•Engineered and manufactured for maximum performance and quality.</li><li>•Made from 100% high-quality plastic to ensure efficient recycling.</li><li>•Inside serration for a strong grip onto bundles.</li><li>•Easy application either manually or with a tensioning tool.</li><li>•Bent tail allows for simpler insertion.</li></ul>
Quantity Per	bag

### Product Description

T-Series Cable Ties feature inside serrations to provide a positive hold on wire and cable bundles. The head design guarantees high tensile strength and a low insertion force. The bent tail design allows quick and simple installations by hand. For high-volume applications, tensioning tools are available to ensure consistent and safe installation.

<b>Short Description</b>	Cable Tie, 8.3" Long, UL Rated, 40lb Tensile Strength, PA66, Natural, 1000/pkg
<b>Global Part Name</b>	T40R(U)-PA66-NA
<b>Minimum Tensile Strength (Imperial)</b>	40.0
<b>Minimum Tensile Strength (Metric)</b>	180.0
<b>Length L (Imperial)</b>	8.3
<b>Length L (Metric)</b>	210.82
<b>Identification Plate Position</b>	none
<b>Releasable Closure</b>	No
<b>Tie Closure</b>	plastic pawl
<b>Variant</b>	Inside Serrated
<b>Width W (Imperial)</b>	0.16
<b>Width W (Metric)</b>	4.0
<b>Bundle Diameter Min (Imperial)</b>	0.06
<b>Bundle Diameter Min (Metric)</b>	1.5
<b>Bundle Diameter Max (Imperial)</b>	2.2
<b>Bundle Diameter Max (Metric)</b>	55.9

<b>Material</b>	Polyamide 6.6 (PA66)
<b>Material Shortcut</b>	PA66
<b>Flammability</b>	UL 94 V2
<b>Halogen free</b>	Yes
<b>Operating Temperature (Metric)</b>	-40°F to +185°F (-40°C to +85°C)
<b>ROHS Complaint</b>	Yes
<b>Certification/Specification WEB</b>	UL-ZODZ2.E64139
<b>UL Recognized (US)</b>	Yes
<b>UL Listed (US and Canada)</b>	Yes
<b>UL Recognized (US and Canada)</b>	Yes
<b>UL Listed (US)</b>	Yes
<b>Package Quantity(Imperial)</b>	1000
<b>Package Quantity (Metric)</b>	1000
<b>Customs Number</b>	3926909988
<b>Weight (Metric)</b>	0.3

---

© 2019 HellermannTyton. All Rights Reserved.

[Contact Us](#) [RoHS/WEEE Compliance](#) [Disclaimer](#) [Terms and Conditions](#)