

Specification Sheet

Part Number: T40L9M4



Cable Tie, 14.6" Long, UL Rated, 40lb Tensile Strength, PA66, Natural, 1000/pkg

Article Number	111-04311
Type	T40L
Color	Natural (NA)
Features & Benefits	<ul style="list-style-type: none">•Engineered and manufactured for maximum performance and quality.•Made from 100% high-quality plastic to ensure efficient recycling.•Inside serration for a strong grip onto bundles.•Easy application either manually or with a tensioning tool.•Bent tail allows for simpler insertion.
Quantity Per	bag

Product Description

T-Series Cable Ties feature inside serrations to provide a positive hold on wire and cable bundles. The head design guarantees high tensile strength and a low insertion force. The bent tail design allows quick and simple installations by hand. For high-volume applications, tensioning tools are available to ensure consistent and safe installation.

Short Description

Cable Tie, 14.6" Long, UL Rated, 40lb Tensile Strength, PA66, Natural, 1000/pkg

Global Part Name

T40L-PA66-NA

Minimum Tensile Strength (Imperial)

40.0

Minimum Tensile Strength (Metric)

180.0

Length L (Imperial)

14.6

Length L (Metric)

370.0

Identification Plate Position

none

Releasable Closure

No

Variant

Inside Serrated

Width W (Imperial)

0.16

Width W (Metric)

4.0

Bundle Diameter Min (Imperial)

0.06

Bundle Diameter Min (Metric)

1.5

Bundle Diameter Max (Imperial)

4.13

Bundle Diameter Max (Metric)

104.9

Material	Polyamide 6.6 (PA66)
Material Shortcut	PA66
Flammability	UL 94 V2
Halogen free	Yes
Operating Temperature (Metric)	-40°F to +185°F (-40°C to +85°C)
ROHS Complaint	Yes
Certification/Specification WEB	UL-ZODZ2.E64139
UL Recognized (US)	Yes
UL Listed (US and Canada)	Yes
UL Recognized (US and Canada)	Yes
UL Listed (US)	Yes
Package Quantity(Imperial)	1000
Package Quantity (Metric)	1000
Customs Number	3926909988

