

Specification Sheet

Part Number: T40I0M4



Cable Tie, 11.6" Long, UL Rated, 40lb Tensile Strength, PA66, Black, 1000/pkg

Article Number	111-04604
Type	T40I
Color	Black (BK)
Features & Benefits	<ul style="list-style-type: none">•Engineered and manufactured for maximum performance and quality.•Made from 100% high-quality plastic to ensure efficient recycling.•Inside serration for a strong grip onto bundles.•Easy application either manually or with a tensioning tool.•Bent tail allows for simpler insertion.
Quantity Per	bag

Product Description

T-Series Cable Ties feature inside serrations to provide a positive hold on wire and cable bundles. The head design guarantees high tensile strength and a low insertion force. The bent tail design allows quick and simple installations by hand. For high-volume applications, tensioning tools are available to ensure consistent and safe installation.

Short Description	Cable Tie, 11.6" Long, UL Rated, 40lb Tensile Strength, PA66, Black, 1000/pkg
Global Part Name	T40I-PA66-BK
Minimum Tensile Strength (Imperial)	40.0
Minimum Tensile Strength (Metric)	180.0
Length L (Imperial)	11.6
Length L (Metric)	295.0
Identification Plate Position	none
Releasable Closure	No
Variant	Inside Serrated
Width W (Imperial)	0.16
Width W (Metric)	4.0
Bundle Diameter Min (Imperial)	0.06
Bundle Diameter Min (Metric)	1.5
Bundle Diameter Max (Imperial)	3.15
Bundle Diameter Max (Metric)	80.0

Material	Polyamide 6.6 (PA66)
Material Shortcut	PA66
Flammability	UL 94 V2
Halogen free	Yes
Operating Temperature (Metric)	-40°F to +185°F (-40°C to +85°C)
ROHS Complaint	Yes
UL Recognized (US)	Yes
UL Listed (US and Canada)	Yes
UL Recognized (US and Canada)	Yes
UL Listed (US)	Yes
Package Quantity(Imperial)	1000
Package Quantity (Metric)	1000
Customs Number	3926909988