

Specification Sheet

Part Number: T50R0C2



Cable Tie, 8" Long, UL Rated, 50lb Tensile Strength, PA66, Black, 100/pkg

Article Number	111-04878
Type	T50R
Color	Black (BK)
Features & Benefits	<ul style="list-style-type: none">•Engineered and manufactured for maximum performance and quality.•Made from 100% high-quality plastic to ensure efficient recycling.•Inside serration for a strong grip onto bundles.•Easy application either manually or with a tensioning tool.•Bent tail allows for simpler insertion.
Quantity Per	bag

Product Description

T-Series Cable Ties feature inside serrations to provide a positive hold on wire and cable bundles. The head design guarantees high tensile strength and a low insertion force. The bent tail design allows quick and simple installations by hand. For high-volume applications, tensioning tools are available to ensure consistent and safe installation.

Short Description	Cable Tie, 8" Long, UL Rated, 50lb Tensile Strength, PA66, Black, 100/pkg
Global Part Name	T50R-PA66-BK
Minimum Tensile Strength (Imperial)	50.0
Minimum Tensile Strength (Metric)	225.0
Length L (Imperial)	8.0
Length L (Metric)	203.2
Identification Plate Position	none
Releasable Closure	No
Tie Closure	plastic pawl
Variant	Inside Serrated
Width W (Imperial)	0.18
Width W (Metric)	4.6
Bundle Diameter Min (Imperial)	0.06
Bundle Diameter Min (Metric)	1.5
Bundle Diameter Max (Imperial)	1.97
Bundle Diameter Max (Metric)	50.0
Thickness T (Metric)	1.2

Material	Polyamide 6.6 (PA66)
-----------------	----------------------

Material Shortcut PA66

US MIL SPEC	MS3367-1-10	Flammability
--------------------	-------------	---------------------

UL 94 V2

Halogen free

Yes

Operating Temperature (Metric)

-40°F to +185°F (-40°C to +85°C)

ROHS Complaint

Yes

UL Recognized (US)

Yes

UL Listed (US and Canada)

Yes

UL Recognized (US and Canada)

Yes

UL Listed (US)

Yes

Package Quantity(Imperial)	100
-----------------------------------	-----

Package Quantity (Metric) 100

Customs Number	3926909988
-----------------------	------------

© 2019 HellermannTyton. All Rights Reserved.

[Contact Us](#) [RoHS/WEEE Compliance](#) [Disclaimer](#) [Terms and Conditions](#)