

## Specification Sheet

Part Number: T50R2UVM4



UV Resistant Cable Tie, 8" Long, UL Rated, 50lb Tensile Strength, PA66UV, Red, 1000/pkg

Article Number	111-04916
Type	T50R
Color	Red (RD)
Features & Benefits	<ul style="list-style-type: none"><li>• UV stabilized cable ties contain an inhibitor which prolongs the life of the tie in UV exposures.</li><li>• Inside serrations allow for strong grip on cables and wire bundles.</li><li>• Head design provides high tensile strength with very low insertion force.</li><li>• Bent tail ensures a quick and simple installation.</li></ul>
Quantity Per	bag

### Product Description

T-Series Cable Ties feature inside serrations to provide a positive hold on wire and cable bundles. The head design guarantees high tensile strength and a low insertion force. The bent tail design allows quick and simple installations by hand. For high-volume applications, tensioning tools are available to ensure consistent and safe installation.

<b>Short Description</b>	UV Resistant Cable Tie, 8" Long, UL Rated, 50lb Tensile Strength, PA66UV, Red, 1000/pkg
<b>Global Part Name</b>	T50R-PA66UV-RD
<b>Minimum Tensile Strength (Imperial)</b>	50.0
<b>Minimum Tensile Strength (Metric)</b>	225.0
<b>Length L (Imperial)</b>	8.0
<b>Length L (Metric)</b>	203.2
<b>Identification Plate Position</b>	none
<b>Releasable Closure</b>	No
<b>Tie Closure</b>	plastic pawl
<b>Variant</b>	Inside Serrated
<b>Width W (Imperial)</b>	0.18
<b>Width W (Metric)</b>	4.6
<b>Bundle Diameter Min (Imperial)</b>	0.06
<b>Bundle Diameter Min (Metric)</b>	1.5
<b>Bundle Diameter Max (Imperial)</b>	1.97
<b>Bundle Diameter Max (Metric)</b>	50.0

**Thickness T (Metric)**

1.2

**Material**

Polyamide 6.6 UV-resistant (PA66UV)

**Material Shortcut**

PA66UV

**US MIL SPEC**

MS3367-1-10

**Flammability**

UL 94 V2

**Halogen free**

Yes

**Operating Temperature (Metric)**

-40°F to +185°F (-40°C to +85°C)

**ROHS Complaint**

Yes

**Certification/Specification WEB**

UL-ZODZ2.E64139

**UL Recognized (US)**

Yes

**UL Recognized (US and Canada)**

Yes

**Package Quantity(Imperial)**

1000

**Package Quantity (Metric)**

1000

**Customs Number**

3926909988

**Content Unit(BMEcat)**

bag

---

© 2019 HellermannTyton. All Rights Reserved.

[Contact Us](#) [RoHS/WEEE Compliance](#) [Disclaimer](#) [Terms and Conditions](#)