

Specification Sheet

Part Number: T50L6M4



Article Number

111-05434

Type

T50L

Color

Blue (BU)

Features & Benefits

- Engineered and manufactured for maximum performance and quality.
- Made from 100% high-quality plastic to ensure efficient recycling.
- Inside serration for a strong grip onto bundles.
- Easy application either manually or with a tensioning tool.
- Bent tail allows for simpler insertion.

Quantity Per

bag

Product Description

T-Series Cable Ties feature inside serrations to provide a positive hold on wire and cable bundles. The head design guarantees high tensile strength and a low insertion force. The bent tail design allows quick and simple installations by hand. For high-volume applications, tensioning tools are available to ensure consistent and safe installation.

Short Description

Cable Tie, 15.35" Long, UL Rated, 50lb Tensile Strength, PA66, Blue, 1000/pkg

Global Part Name

T50L-PA66-BU

Minimum Tensile Strength (Imperial)

50.0

Minimum Tensile Strength (Metric)

225.0

Length L (Imperial)

15.35

Length L (Metric)

389.89

Identification Plate Position

none

Releasable Closure

No

Tie Closure

plastic pawl

Variant

Inside Serrated

Width W (Imperial)

0.19

Width W (Metric)

4.8

Bundle Diameter Min (Imperial)

0.06

Bundle Diameter Min (Metric)

1.5

Bundle Diameter Max (Imperial)

4.3

Bundle Diameter Max (Metric)

109.2

Thickness T (Metric)

1.4

Material	Polyamide 6.6 (PA66)
-----------------	----------------------

Material Shortcut	PA66
--------------------------	------

US MIL SPEC	SAE-AS33671
--------------------	-------------

MS3367-2-6

Flammability

UL 94 V2

Halogen free

Yes

Operating Temperature (Metric)

-40°F to +185°F (-40°C to +85°C)

ROHS Complaint

Yes

Certification/Specification WEB

UL-ZODZ.E64139 CAGE Code 53421

UL Recognized (US)

Yes

UL Listed (US and Canada)

Yes

UL Recognized (US and Canada)

Yes

Package Quantity(Imperial)	1000
-----------------------------------	------

Package Quantity (Metric)	1000
----------------------------------	------

Customs Number	3926909988
-----------------------	------------

© 2019 HellermannTyton. All Rights Reserved.

[Contact Us](#) [RoHS/WEEE Compliance](#) [Disclaimer](#) [Terms and Conditions](#)