

Specification Sheet

Part Number: T120I9K2



Heavy Duty Cable Tie, 11.8" Long, UL Rated, 120lb Tensile Strength, PA66, Natural, 50/pkg

Article Number	111-12211
Type	T120I
Color	Natural (NA)
Features & Benefits	<ul style="list-style-type: none">•Engineered and manufactured for maximum performance and quality.•Made from 100% high-quality plastic to ensure efficient recycling.•Inside serration for a strong grip onto bundles.•Easy application either manually or with a tensioning tool.•Bent tail allows for simpler insertion.
Quantity Per	bag

Product Description

Heavy-Duty T-Series Cable Ties feature inside serrations to provide a positive hold on wire and cable bundles. Durable head design guarantees high tensile strength and a low insertion force. The bent tail allows quick and simple installations by hand. For high-volume applications, tensioning tools are available to ensure consistent and safe installation.

Short Description

Heavy Duty Cable Tie, 11.8" Long, UL Rated, 120lb Tensile Strength, PA66, Natural, 50/pkg

Global Part Name

T120I-PA66-NA

Minimum Tensile Strength (Imperial)

120.0

Minimum Tensile Strength (Metric)

535.0

Length L (Imperial)

11.8

Length L (Metric)

300.0

Identification Plate Position

none

Releasable Closure

No

Tie Closure

plastic pawl

Variant

Inside Serrated

Width W (Imperial)

0.30

Width W (Metric)

7.6

Bundle Diameter Min (Imperial)

0.20

Bundle Diameter Min (Metric)

5.0

Bundle Diameter Max (Imperial)

3.2

Bundle Diameter Max (Metric)

81.3

Thickness T (Imperial)	0.06
Thickness T (Metric)	1.6
Cable Tie Width Max (Imperial)	0.3
Cable Tie Width Max (Metric)	7.61
Material	Polyamide 6.6 (PA66)
Material Shortcut	PA66
Flammability	UL 94 V2
Halogen free	Yes
Operating Temperature (Metric)	-40°F to +185°F (-40°C to +85°C)
ROHS Complaint	Yes
Certification/Specification WEB	UL ANSI/UL 62275 UL ANSI/UL 746B UL ANSI/UL 1565
UL Recognized (US)	Yes
UL Listed (US and Canada)	Yes
UL Recognized (US and Canada)	Yes
UL Listed (US)	Yes

Package Quantity(Imperial)

50

Package Quantity (Metric)

50

Customs Number

3926909988