

## Specification Sheet

Part Number: T120I9H4



Heavy Duty Cable Tie, 11.8" Long, UL Rated, 120lb Tensile Strength, PA66, Natural, 500/pkg

Article Number	111-12213
Type	T120I
Color	Natural (NA)
Features & Benefits	<ul style="list-style-type: none"><li>•Engineered and manufactured for maximum performance and quality.</li><li>•Made from 100% high-quality plastic to ensure efficient recycling.</li><li>•Inside serration for a strong grip onto bundles.</li><li>•Easy application either manually or with a tensioning tool.</li><li>•Bent tail allows for simpler insertion.</li></ul>
Quantity Per	bag

### Product Description

Heavy-Duty T-Series Cable Ties feature inside serrations to provide a positive hold on wire and cable bundles. Durable head design guarantees high tensile strength and a low insertion force. The bent tail allows quick and simple installations by hand. For high-volume applications, tensioning tools are available to ensure consistent and safe installation.

<b>Short Description</b>	Heavy Duty Cable Tie, 11.8" Long, UL Rated, 120lb Tensile Strength, PA66, Natural, 500/pkg
<b>Global Part Name</b>	T120I-PA66-NA
<b>Minimum Tensile Strength (Imperial)</b>	120.0
<b>Minimum Tensile Strength (Metric)</b>	535.0
<b>Length L (Imperial)</b>	11.8
<b>Length L (Metric)</b>	300.0
<b>Identification Plate Position</b>	none
<b>Releasable Closure</b>	No
<b>Tie Closure</b>	plastic pawl
<b>Variant</b>	Inside Serrated
<b>Width W (Imperial)</b>	0.30
<b>Width W (Metric)</b>	7.6
<b>Bundle Diameter Min (Imperial)</b>	0.20
<b>Bundle Diameter Min (Metric)</b>	5.0
<b>Bundle Diameter Max (Imperial)</b>	3.2
<b>Bundle Diameter Max (Metric)</b>	81.3

<b>Thickness T (Metric)</b>	1.6
<b>Cable Tie Width Max (Imperial)</b>	0.3
<b>Cable Tie Width Max (Metric)</b>	7.61
<b>Material</b>	Polyamide 6.6 (PA66)
<b>Material Shortcut</b>	PA66
<b>Flammability</b>	UL 94 V2
<b>Halogen free</b>	Yes
<b>Operating Temperature (Metric)</b>	-40°F to +185°F (-40°C to +85°C)
<b>ROHS Complaint</b>	Yes
<b>Certification/Specification WEB</b>	UL   ANSI/UL 62275 UL   ANSI/UL 1565 UL   ANSI/UL 746B
<b>UL Recognized (US)</b>	Yes
<b>UL Listed (US and Canada)</b>	Yes
<b>UL Recognized (US and Canada)</b>	Yes
<b>UL Listed (US)</b>	Yes
<b>Package Quantity(Imperial)</b>	500

**Package Quantity (Metric)**

500

**Customs Number**

3926909988