

Specification Sheet

Part Number: 111-12761



Made from 100% high-quality plastic to ensure efficient recycling.

Inside serrations produce strong grip on cables and wire bundles.

Easy application either manually or with a tensioning tool.

Bent tail ensures a quick and simple installation.

Cable Tie, 20.9" Long, 120lb Tensile Strength, PA66, Natural, 100/pkg

Article Number 111-12761

Type T120X

Color Natural (NA)

Quantity Per bag

Product Description Heavy-Duty T-Series Cable Ties feature inside serrations to provide a positive hold on wire and cable bundles. Durable head design guarantees high tensile strength and a low insertion force. The bent tail allows quick and simple installations by hand. For high-volume applications, tensioning tools are available to ensure consistent and safe installation.

Short Description Cable Tie, 20.9" Long, 120lb Tensile Strength, PA66, Natural, 100/pkg

Global Part Name	T120X-PA66-NA
Minimum Tensile Strength (Imperial)	120
Minimum Tensile Strength (Metric)	535
Length L (Imperial)	20.9
Length L (Metric)	530
Identification Plate Position	none
Releasable Closure	No
Variant	Inside Serrated
Width W (Imperial)	0.30
Width W (Metric)	7.6
Bundle Diameter Min (Imperial)	0.19
Bundle Diameter Min (Metric)	4.8
Bundle Diameter Max (Imperial)	5.94
Bundle Diameter Max (Metric)	151
Thickness T (Imperial)	0.07
Thickness T (Metric)	1.9

Material	Polyamide 6.6 (PA66)
Material Shortcut	PA66
Use Conditions	For Indoor Use Only
Operating Temperature	-40°F to +185°F (-40°C to +85°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Package Quantity (Imperial)	100
Package Quantity (Metric)	100
Customs Number	3926909988