

Specification Sheet

Part Number: T120S0HSH4



Heavy Duty Cable Tie, 8.9" Long, UL Rated, 120lb Tensile Strength, PA66HS, Black, 500/pkg

Article Number	111-12821
Type	T120S
Color	Black (BK)
Features & Benefits	<ul style="list-style-type: none">• Heat stabilized heavy duty cable ties provide excellent resistance to high heat exposures.• Head design provides high tensile strength with very low insertion force.• Bent tail ensures a quick and simple installation.
Quantity Per	bag

Product Description

Heavy-Duty T-Series Cable Ties feature inside serrations to provide a positive hold on wire and cable bundles. Durable head design guarantees high tensile strength and a low insertion force. The bent tail allows quick and simple installations by hand. For high-volume applications, tensioning tools are available to ensure consistent and safe installation.

Short Description

Heavy Duty Cable Tie, 8.9" Long, UL Rated, 120lb Tensile Strength, PA66HS, Black, 500/pkg

Global Part Name

T120S-PA66HS-BK

Minimum Tensile Strength (Imperial)

120.0

Minimum Tensile Strength (Metric)

535.0

Length L (Imperial)

8.9

Length L (Metric)

226.06

Identification Plate Position

none

Releasable Closure

No

Tie Closure

plastic pawl

Variant

Inside Serrated

Width W (Imperial)

0.30

Width W (Metric)

7.6

Bundle Diameter Min (Imperial)

0.20

Bundle Diameter Min (Metric)

5.0

Bundle Diameter Max (Imperial)

2.2

Bundle Diameter Max (Metric)

55.9

Thickness T (Metric)	1.6
Material	Polyamide 6.6 heat stabilized (PA66HS)
Material Shortcut	PA66HS
Flammability	UL 94 V2
Halogen free	Yes
Operating Temperature (Metric)	-40°F to +257°F (-40°C to +125°C)
Reach Complaint(Article 33)	Yes
ROHS Complaint	Yes
Certification/Specification WEB	UL-ZODZ2.E64139
UL Recognized (US)	Yes
UL Listed (US and Canada)	Yes
UL Recognized (US and Canada)	Yes
UL Listed (US)	Yes
Package Quantity(Imperial)	500
Package Quantity (Metric)	500

Customs Number

3926909988

Content Unit(BMEcat)

pcs.