

Specification Sheet

Part Number: T150XL9X2



Heavy Duty Cable Tie, 43.1" Long, UL Rated, 175lb Tensile Strength, PA66, Natural, 25/pkg

Article Number	111-15519
Type	T150XL
Color	Natural (NA)
Features & Benefits	<ul style="list-style-type: none">•Engineered and manufactured for maximum performance and quality.•Made from 100% high-quality plastic to ensure efficient recycling.•Inside serration for a strong grip onto bundles.•Easy application either manually or with a tensioning tool.•Bent tail allows for simpler insertion.
Quantity Per	bag

Product Description

HellermannTyton heavy duty cable ties offer a higher tensile strength for heavy load applications. The head design guarantees high tensile strength, as well as a low insertion force. For high volume applications, tensioning tools are available to ensure consistent and safe installation.

Short Description

Heavy Duty Cable Tie, 43.1" Long, UL Rated, 175lb Tensile Strength, PA66, Natural, 25/pkg

Global Part Name

T150XL-PA66-NA

Minimum Tensile Strength (Imperial)

175.0

Minimum Tensile Strength (Metric)

780.0

Length L (Imperial)

43.1

Length L (Metric)

1095.0

Identification Plate Position

none

Releasable Closure

No

Tie Closure

plastic pawl

Variant

Inside Serrated

Width W (Imperial)

0.35

Width W (Metric)

8.9

Bundle Diameter Min (Imperial)

6.0

Bundle Diameter Min (Metric)

152.0

Bundle Diameter Max (Imperial)

13.0

Bundle Diameter Max (Metric)

330.2

Thickness T (Imperial)	0.083
Thickness T (Metric)	2.1
Material	Polyamide 6.6 (PA66)
Material Shortcut	PA66
Flammability	UL 94 V2
Halogen free	Yes
Operating Temperature (Metric)	-40°F to +185°F (-40°C to +85°C)
Reach Complaint(Article 33)	Yes
ROHS Complaint	Yes
Certification/Specification WEB	UL ANSI/UL 746B UL ANSI/UL 1565 UL ANSI/UL 62275
UL Recognized (US)	Yes
UL Recognized (US and Canada)	Yes
Package Quantity(Imperial)	25
Package Quantity (Metric)	25
Customs Number	3926909988

Content Unit(BMEcat)

pcs.

Weight (Metric)

20.8