

Specification Sheet

Part Number: T250L0X2



Article Number

111-24601

Type

T250L

Color

Black (BK)

Features & Benefits

- Engineered and manufactured for maximum performance and quality.
- Made from 100% high-quality plastic to ensure efficient recycling.
- Inside serration for a strong grip onto bundles.
- Easy application either manually or with a tensioning tool.
- Bent tail allows for simpler insertion.

Quantity Per

bag

Product Description

These cable ties offer a high minimum tensile strength and have a buckle feature which allows the end of the cable tie to be tucked away if necessary. The buckle also snaps into HellermannTyton lashing tie mounts (LTM.) T-Series Cable Ties feature inside serrations to provide a positive hold on wire and cable bundles. The head design guarantees high tensile strength and a low insertion force. The bent tail design allows quick and simple installations by hand. For high-volume applications, tensioning tools are available to ensure consistent and safe installation.

Short Description

Heavy Duty Cable Tie, 34.7" Long, UL Rated, 250lb Tensile Strength, PA66, Black, 25/pkg

Global Part Name

T250L-PA66-BK

Minimum Tensile Strength (Imperial)

250.0

Minimum Tensile Strength (Metric)

1115.0

Length L (Imperial)

34.7

Length L (Metric)

880.0

Identification Plate Position

none

Releasable Closure

No

Tie Closure

plastic pawl

Variant

Inside Serrated

Width W (Imperial)

0.49

Width W (Metric)

12.4

Bundle Diameter Min (Imperial)

0.47

Bundle Diameter Min (Metric)

12.0

Bundle Diameter Max (Imperial)

10.0

Bundle Diameter Max (Metric)

254.0

Material	Polyamide 6.6 (PA66)
Material Shortcut	PA66
Flammability	UL 94 V2
Halogen free	Yes
Operating Temperature (Metric)	-40°F to +185°F (-40°C to +85°C)
Reach Complaint(Article 33)	Yes
ROHS Complaint	Yes
Certification/Specification WEB	UL ANSI/UL 746B UL ANSI/UL 1565 UL ANSI/UL 62275
UL Recognized (US)	Yes
UL Recognized (US and Canada)	Yes
Package Quantity(Imperial)	25
Package Quantity (Metric)	25
Customs Number	3926909988
Content Unit(BMEcat)	pcs.
Weight (Metric)	15.5

© 2019 HellermannTyton. All Rights Reserved.

[Contact Us](#) [RoHS/WEEE Compliance](#) [Disclaimer](#) [Terms and Conditions](#)