

## Specification Sheet

Part Number: T250S0X2



Heavy Duty Cable Tie, 9.1" Long, UL Rated, 250lb Tensile Strength, PA66, Black, 25/pkg

Article Number	111-24700
Type	T250S
Color	Black (BK)
Features & Benefits	<ul style="list-style-type: none"><li>•Engineered and manufactured for maximum performance and quality.</li><li>•Made from 100% high-quality plastic to ensure efficient recycling.</li><li>•Inside serration for a strong grip onto bundles.</li><li>•Easy application either manually or with a tensioning tool.</li><li>•Bent tail allows for simpler insertion.</li></ul>
Quantity Per	bag

**Product Description**

These cable ties offer a high minimum tensile strength and have a buckle feature which allows the end of the cable tie to be tucked away if necessary. The buckle also snaps into HellermannTyton lashing tie mounts (LTM.) T-Series Cable Ties feature inside serrations to provide a positive hold on wire and cable bundles. The head design guarantees high tensile strength and a low insertion force. The bent tail design allows quick and simple installations by hand. For high-volume applications, tensioning tools are available to ensure consistent and safe installation.

**Short Description**

Heavy Duty Cable Tie, 9.1" Long, UL Rated, 250lb Tensile Strength, PA66, Black, 25/pkg

**Global Part Name**

T250S-PA66-BK

**Minimum Tensile Strength (Imperial)**

250.0

**Minimum Tensile Strength (Metric)**

1115.0

**Length L (Imperial)**

9.1

**Length L (Metric)**

230.0

**Identification Plate Position**

none

**Releasable Closure**

No

**Variant**

Inside Serrated

**Width W (Imperial)**

0.49

**Width W (Metric)**

12.4

**Bundle Diameter Min (Imperial)**

0.47

**Bundle Diameter Min (Metric)**

12.0

**Bundle Diameter Max (Imperial)** 1.97

**Bundle Diameter Max (Metric)** 50.0

**Material** Polyamide 6.6 (PA66)

**Material Shortcut** PA66

**Flammability** UL 94 V2

**Halogen free** Yes

**Operating Temperature (Metric)** -40°F to +185°F (-40°C to +85°C)

**ROHS Complaint** Yes

**Certification/Specification WEB** UL-ZODZ2.E64139

**UL Recognized (US)** Yes

**UL Recognized (US and Canada)** Yes

**Package Quantity(Imperial)** 25

**Package Quantity (Metric)** 25

**Customs Number** 3926909988

---

© 2019 HellermannTyton. All Rights Reserved.

[Contact Us](#) [RoHS/WEEE Compliance](#) [Disclaimer](#) [Terms and Conditions](#)