

Specification Sheet

Part Number: T250S9X2



Heavy Duty Cable Tie, 9.1" Long, UL Rated, 250lb Tensile Strength, PA66, Natural, 25/pkg

Article Number	111-24702
Type	T250S
Color	Natural (NA)
Features & Benefits	<ul style="list-style-type: none">•Engineered and manufactured for maximum performance and quality.•Made from 100% high-quality plastic to ensure efficient recycling.•Inside serration for a strong grip onto bundles.•Easy application either manually or with a tensioning tool.•Bent tail allows for simpler insertion.
Quantity Per	bag

Product Description

These cable ties offer a high minimum tensile strength and have a buckle feature which allows the end of the cable tie to be tucked away if necessary. The buckle also snaps into HellermannTyton lashing tie mounts (LTM.) T-Series Cable Ties feature inside serrations to provide a positive hold on wire and cable bundles. The head design guarantees high tensile strength and a low insertion force. The bent tail design allows quick and simple installations by hand. For high-volume applications, tensioning tools are available to ensure consistent and safe installation.

Short Description

Heavy Duty Cable Tie, 9.1" Long, UL Rated, 250lb Tensile Strength, PA66, Natural, 25/pkg

Global Part Name

T250S-PA66-NA

Minimum Tensile Strength (Imperial)

250.0

Minimum Tensile Strength (Metric)

1115.0

Length L (Imperial)

9.1

Length L (Metric)

230.0

Identification Plate Position

none

Releasable Closure

No

Variant

Inside Serrated

Width W (Imperial)

0.49

Width W (Metric)

12.4

Bundle Diameter Min (Imperial)

0.47

Bundle Diameter Min (Metric)

12.0

Bundle Diameter Max (Imperial) 1.97

Bundle Diameter Max (Metric) 50.0

Material Polyamide 6.6 (PA66)

Material Shortcut PA66

Flammability UL 94 V2

Halogen free Yes

Operating Temperature (Metric) -40°F to +185°F (-40°C to +85°C)

ROHS Complaint Yes

Certification/Specification WEB UL-ZODZ2.E64139

UL Recognized (US) Yes

UL Recognized (US and Canada) Yes

Package Quantity(Imperial) 25

Package Quantity (Metric) 25

Customs Number 3926909988

© 2019 HellermannTyton. All Rights Reserved.

[Contact Us](#) [RoHS/WEEE Compliance](#) [Disclaimer](#) [Terms and Conditions](#)