

Specification Sheet

Part Number: T250XL0X2



Heavy Duty Cable Tie, 40.6" Long, UL Rated, 250lb Tensile Strength, PA66, Black, 25/pkg

Article Number	111-25200
Type	T250XL
Color	Black (BK)
Features & Benefits	<ul style="list-style-type: none">•Engineered and manufactured for maximum performance and quality.•Made from 100% high-quality plastic to ensure efficient recycling.•Inside serration for a strong grip onto bundles.•Easy application either manually or with a tensioning tool.•Bent tail allows for simpler insertion.
Quantity Per	bag

Product Description

These cable ties offer a high minimum tensile strength and have a buckle feature which allows the end of the cable tie to be tucked away if necessary. The buckle also snaps into HellermannTyton lashing tie mounts (LTM.) T-Series Cable Ties feature inside serrations to provide a positive hold on wire and cable bundles. The head design guarantees high tensile strength and a low insertion force. The bent tail design allows quick and simple installations by hand. For high-volume applications, tensioning tools are available to ensure consistent and safe installation.

Short Description

Heavy Duty Cable Tie, 40.6" Long, UL Rated, 250lb Tensile Strength, PA66, Black, 25/pkg

Global Part Name

T250XL-PA66-BK

Minimum Tensile Strength (Imperial)

250.0

Minimum Tensile Strength (Metric)

1115.0

Length L (Imperial)

40.6

Length L (Metric)

1030.0

Identification Plate Position

none

Releasable Closure

No

Tie Closure

plastic pawl

Variant

Inside Serrated

Width W (Imperial)

0.49

Width W (Metric)

12.4

Bundle Diameter Min (Imperial)

0.47

Bundle Diameter Min (Metric) 12.0

Bundle Diameter Max (Imperial) 12.0

Bundle Diameter Max (Metric) 305.0

Material Polyamide 6.6 (PA66)

Material Shortcut PA66

Flammability UL 94 V2

Halogen free Yes

Operating Temperature (Metric) -40°F to +185°F (-40°C to +85°C)

Reach Complaint(Article 33) Yes

ROHS Complaint Yes

Certification/Specification WEB UL | ANSI/UL 1565 UL | ANSI/UL 746B UL | ANSI/UL 62275

UL Recognized (US) Yes

UL Recognized (US and Canada) Yes

Package Quantity(Imperial) 25

Package Quantity (Metric) 25

Customs Number

3926909988

Content Unit(BMEcat)

pcs.

Weight (Metric)

15.436