

Specification Sheet

Part Number: T250I9X2



Heavy Duty Cable Tie, 28.7" Long, UL Rated, 250lb Tensile Strength, PA66, Natural, 25/pkg

Article Number	111-25219
Type	T250I
Color	Natural (NA)
Features & Benefits	<ul style="list-style-type: none">•Engineered and manufactured for maximum performance and quality.•Made from 100% high-quality plastic to ensure efficient recycling.•Inside serration for a strong grip onto bundles.•Easy application either manually or with a tensioning tool.•Bent tail allows for simpler insertion.
Quantity Per	bag

Product Description

These cable ties offer a high minimum tensile strength and have a buckle feature which allows the end of the cable tie to be tucked away if necessary. The buckle also snaps into HellermannTyton lashing tie mounts (LTM.) T-Series Cable Ties feature inside serrations to provide a positive hold on wire and cable bundles. The head design guarantees high tensile strength and a low insertion force. The bent tail design allows quick and simple installations by hand. For high-volume applications, tensioning tools are available to ensure consistent and safe installation.

Short Description

Heavy Duty Cable Tie, 28.7" Long, UL Rated, 250lb Tensile Strength, PA66, Natural, 25/pkg

Global Part Name

T250I-PA66-NA

Minimum Tensile Strength (Imperial)

250.0

Minimum Tensile Strength (Metric)

1115.0

Length L (Imperial)

28.7

Length L (Metric)

730.0

Identification Plate Position

none

Releasable Closure

No

Variant

Inside Serrated

Width W (Imperial)

0.49

Width W (Metric)

12.4

Bundle Diameter Min (Imperial)

0.47

Bundle Diameter Min (Metric)

12.0

Bundle Diameter Max (Imperial)	8.0
Bundle Diameter Max (Metric)	203.0
Material	Polyamide 6.6 (PA66)
Material Shortcut	PA66
Flammability	UL 94 V2
Halogen free	Yes
Operating Temperature (Metric)	-40°F to +185°F (-40°C to +85°C)
Reach Complaint(Article 33)	Yes
ROHS Complaint	Yes
Certification/Specification WEB	UL ANSI/UL 62275 UL ANSI/UL 1565 UL ANSI/UL 746B
UL Recognized (US)	Yes
UL Recognized (US and Canada)	Yes
Package Quantity(Imperial)	25
Package Quantity (Metric)	25
Customs Number	3926909988

Content Unit(BMEcat)

pcs.

Weight (Metric)

17.6