

Specification Sheet

Part Number: TELS-SPK2



Extended-Length Tie Spacer, PP, Black, 50/pkg

Article Number	111-32000
Type	EL-TY (TELS-SPK2)
Color	Black (BK)
Features & Benefits	<ul style="list-style-type: none">• Spacers provide distance between two bundles.• Continuous strap and separate heads allow for any bundle diameter, eliminating waste.• Smooth strap prevents cable damage.• UV resistant materials contain an inhibitor which prolongs the life of the tie in outdoor environments.
Quantity Per	bag

Product Description

Extended Length Ties provide a high tensile strength strapping system consisting of a continuous strap and separate locking head making it suitable for any bundle diameter, eliminating waste. The smooth strap and specially designed heads with stainless steel pawls provide a strong grip on cables and wires without damage during vibration or in extreme environments. Spacers are available for dual bundle applications.

Short Description	Extended-Length Tie Spacer, PP, Black, 50/pkg
Global Part Name	EL-TY (TELS-SPK2)-PP-BK
Minimum Tensile Strength (Imperial)	250.0
Length L (Imperial)	1.2
Length L (Metric)	30.5
Fixation Method	2 piece
Identification Plate Position	none
Releasable Closure	No
Tie Closure	steel pawl
Variant	Extended Length
Width W (Imperial)	2.1
Width W (Metric)	53.3
Height H (Imperial)	0.67
Height H (Metric)	17.0
Cable Tie Width Max (Metric)	12.7

Material	Polypropylene (PP)
Material Shortcut	PP
Material Head	Polyacetal, UV stabilized (POMUV) with stainless steel pawl (SS)
Flammability	UL 94 HB
Operating Temperature (Metric)	-40°F to +239°F (-40°C to +115°C)
Reach Complaint(Article 33)	Yes
ROHS Complaint	Yes
Package Quantity(Imperial)	50
Package Quantity (Metric)	50
Customs Number	3926909988
Content Unit(BMEcat)	pcs.
Weight (Metric)	0.6