

Specification Sheet

Part Number: IT18R3L4



Identification Tie, 3.9" Long, 18lb Tensile Strength, PA66, Orange, 200/pkg

Article Number	111-81811
Type	IT18R
Color	Orange (OG)
Features & Benefits	<ul style="list-style-type: none">• Identification plate feature allows bundles to be easily marked and identified.• Wire and cable harnesses can be secured and identified using just one product, which saves time.• Plates can be marked manually with a permanent marker or with a pre-printed adhesive label.
Quantity Per	bag

Product Description

Identification Cable Ties feature an identification plate that allows wire and cable bundles to be easily marked and identified. These ties enable wire and cables to be secured and identified using just one product, saving installation time. The plates can be marked using a permanent marker or with a HellermannTyton adhesive label.

Short Description	Identification Tie, 3.9" Long, 18lb Tensile Strength, PA66, Orange, 200/pkg
Global Part Name	IT18R-PA66-OG
Minimum Tensile Strength (Imperial)	18.0
Minimum Tensile Strength (Metric)	80.0
Length L (Imperial)	3.9
Length L (Metric)	100.0
Fixation Method	Others
Identification Plate Position	attached to bundle
Releasable Closure	No
Tie Closure	plastic pawl
Variant	Inside Serrated
Width W (Imperial)	0.98
Width W (Metric)	25.0
Bundle Diameter Min (Imperial)	0.19
Bundle Diameter Min (Metric)	4.8
Bundle Diameter Max (Imperial)	0.75
Bundle Diameter Max (Metric)	19.0

Height H (Imperial) 0.32

Height H (Metric) 8.0

Outside Diameter Max(Imperial) 0.87

Outside Diameter Min (metric) 6.00

Outside Diameter Min(Imperial) 0.24

Outside Diameter Max (metric) 22.00

Material Polyamide 6.6 (PA66)

Material Shortcut PA66

US MIL SPEC MS3368-5-3E

SAE-AS33681

Flammability

UL 94 V2

Halogen free

Yes

Operating Temperature (Metric)

-40°F to +185°F (-40°C to +85°C)

Reach Complaint(Article 33)

No

ROHS Complaint

Yes

Certification/Specification WEB

UL-ZODZ2.E64139 CAGE Code 53421

UL Recognized (US)

Yes

UL Recognized (US and Canada)

Yes

Package Quantity(Imperial)

200

Package Quantity (Metric)

200

Customs Number

3926909988