

Specification Sheet

Part Number: IT18R0UVC2



Identification Tie, 3.9" Long, 18lb Tensile Strength, PA66UV, Black, 100/pkg

Article Number

111-81826

Type

IT18R

Color

Black (BK)

Features & Benefits

- UV stabilized cable ties provide excellent resistance to UV exposures.
- Identification plate feature allows bundles to be easily marked and identified.
- Wire and cable harnesses can be secured and identified using just one product, which saves time.
- Plates can be marked manually with a permanent marker or with a pre-printed adhesive label.

Quantity Per

bag

Product Description

Identification Cable Ties feature an identification plate that allows wire and cable bundles to be easily marked and identified. These ties enable wire and cables to be secured and identified using just one product, saving installation time. The plates can be marked using a permanent marker or with a HellermannTyton adhesive label.

| | |
|--|--|
| Short Description | Identification Tie, 3.9" Long, 18lb Tensile Strength, PA66UV, Black, 100/pkg |
| Global Part Name | IT18R-PA66UV-BK |
| Minimum Tensile Strength (Imperial) | 18.0 |
| Minimum Tensile Strength (Metric) | 80.0 |
| Length L (Imperial) | 3.9 |
| Length L (Metric) | 100.0 |
| Fixation Method | Others |
| Identification Plate Position | attached to bundle |
| Releasable Closure | No |
| Tie Closure | plastic pawl |
| Variant | Inside Serrated |
| Width W (Imperial) | 0.98 |
| Width W (Metric) | 25.0 |
| Bundle Diameter Min (Imperial) | 0.19 |
| Bundle Diameter Min (Metric) | 4.8 |
| Bundle Diameter Max (Imperial) | 0.75 |
| Bundle Diameter Max (Metric) | 19.0 |

Height H (Imperial) 0.32

Height H (Metric) 8.0

Outside Diameter Max(Imperial) 0.87

Outside Diameter Min (metric) 6.00

Outside Diameter Min(Imperial) 0.24

Outside Diameter Max (metric) 22.00

Material Polyamide 6.6 UV-resistant (PA66UV)

Material Shortcut PA66UV

US MIL SPEC SAE-AS33681

MS3368-5-0E

Flammability

UL 94 V2

Halogen free

Yes

Operating Temperature (Metric)

-40°F to +185°F (-40°C to +85°C)

Reach Complaint(Article 33)

No

ROHS Complaint

Yes

Certification/Specification WEB

CAGE Code 53421 UL-ZODZ2.E64139

UL Recognized (US)

Yes

UL Recognized (US and Canada)

Yes

Package Quantity(Imperial)

100

Package Quantity (Metric)

100

Customs Number

3926909988