

Specification Sheet

Part Number: IT18FL0C2



Identification Tie, 4.3" Long, 18lb Tensile Strength, PA66, Black, 100/pkg

| | |
|---------------------|--|
| Article Number | 111-81910 |
| Type | IT18FL |
| Color | Black (BK) |
| Features & Benefits | <ul style="list-style-type: none">• Identification plate feature allows bundles to be easily marked and identified.• Wire and cable harnesses can be secured and identified using just one product, which saves time.• Plates can be marked manually with a permanent marker or with a pre-printed adhesive label. |
| Quantity Per | bag |

Product Description

Identification Cable Ties feature an identification plate that allows wire and cable bundles to be easily marked and identified. These ties enable wire and cables to be secured and identified using just one product, saving installation time. The plates can be marked using a permanent marker or with a HellermannTyton adhesive label.

| | |
|--|--|
| Short Description | Identification Tie, 4.3" Long, 18lb Tensile Strength, PA66, Black, 100/pkg |
| Global Part Name | IT18FL-PA66-BK |
| Minimum Tensile Strength (Imperial) | 18.0 |
| Minimum Tensile Strength (Metric) | 80.0 |
| Length L (Imperial) | 4.3 |
| Length L (Metric) | 110.0 |
| Fixation Method | Others |
| Identification Plate Position | stands of bundle |
| Releasable Closure | No |
| Tie Closure | plastic pawl |
| Variant | Inside Serrated |
| Width W (Imperial) | 0.81 |
| Width W (Metric) | 20.5 |
| Bundle Diameter Min (Imperial) | 0.06 |
| Bundle Diameter Min (Metric) | 1.5 |
| Bundle Diameter Max (Imperial) | 0.75 |
| Bundle Diameter Max (Metric) | 19.0 |

Height H (Imperial) 0.35

Height H (Metric) 9.0

Outside Diameter Max(Imperial) 0.75

Outside Diameter Min (metric) 1.50

Outside Diameter Min(Imperial) 0.059

Outside Diameter Max (metric) 19.00

Material Polyamide 6.6 (PA66)

Material Shortcut PA66

Flammability UL 94 V2

Halogen free Yes

Operating Temperature (Metric) -40°F to +185°F (-40°C to +85°C)

Reach Complaint(Article 33) Yes

ROHS Complaint Yes

UL Recognized (US) Yes

UL Recognized (US and Canada) Yes

Package Quantity(Imperial)

100

Package Quantity (Metric)

100

Customs Number

3926909988

Content Unit(BMEcat)

pcs.

Weight (Metric)

0.3