

Specification Sheet

Part Number: IT18FL10L4



Identification Tie, 4.3" Long, 18lb Tensile Strength, PA66, White, 200/pkg

Article Number	111-81912
Type	IT18FL
Color	White (WH)
Features & Benefits	<ul style="list-style-type: none">• Identification plate feature allows bundles to be easily marked and identified.• Wire and cable harnesses can be secured and identified using just one product, which saves time.• Plates can be marked manually with a permanent marker or with a pre-printed adhesive label.
Quantity Per	bag

Product Description

Identification Cable Ties feature an identification plate that allows wire and cable bundles to be easily marked and identified. These ties enable wire and cables to be secured and identified using just one product, saving installation time. The plates can be marked using a permanent marker or with a HellermannTyton adhesive label.

Short Description	Identification Tie, 4.3" Long, 18lb Tensile Strength, PA66, White, 200/pkg
Global Part Name	IT18FL-PA66-WH
Minimum Tensile Strength (Imperial)	18.0
Minimum Tensile Strength (Metric)	80.0
Length L (Imperial)	4.3
Length L (Metric)	110.0
Fixation Method	Others
Identification Plate Position	stands of bundle
Releasable Closure	No
Tie Closure	plastic pawl
Variant	Inside Serrated
Width W (Imperial)	0.81
Width W (Metric)	20.5
Bundle Diameter Min (Imperial)	0.06
Bundle Diameter Min (Metric)	1.5
Bundle Diameter Max (Imperial)	0.75
Bundle Diameter Max (Metric)	19.0

Height H (Imperial) 0.35

Height H (Metric) 9.0

Outside Diameter Max(Imperial) 0.75

Outside Diameter Min (metric) 1.50

Outside Diameter Min(Imperial) 0.059

Outside Diameter Max (metric) 19.00

Material Polyamide 6.6 (PA66)

Material Shortcut PA66

Flammability UL 94 V2

Halogen free Yes

Operating Temperature (Metric) -40°F to +185°F (-40°C to +85°C)

Reach Complaint(Article 33) No

ROHS Complaint Yes

Certification/Specification WEB UL

UL Recognized (US) Yes

UL Recognized (US and Canada) Yes

Package Quantity(Imperial)

200

Package Quantity (Metric)

200

Customs Number

3926909988