

Specification Sheet

Part Number: IT50RD0K2



Identification Tie, 8" Long, 50lb Tensile Strength, PA66, Black, 50/pkg

Article Number

111-85201

Type

IT50RD

Color

Black (BK)

Features & Benefits

- Identification plate feature allows bundles to be easily marked and identified.
- Wire and cable harnesses can be secured and identified using just one product, which saves time.
- Plates can be marked manually with a permanent marker or with a pre-printed adhesive label.

Quantity Per

bag

Product Description

Identification Cable Ties feature an identification plate that allows wire and cable bundles to be easily marked and identified. These ties enable wire and cables to be secured and identified using just one product, saving installation time. The plates can be marked using a permanent marker or with a HellermannTyton adhesive label.

Short Description

Identification Tie, 8" Long, 50lb Tensile Strength, PA66, Black, 50/pkg

Global Part Name

IT50RD-PA66-BK

Minimum Tensile Strength (Imperial)

50.0

Minimum Tensile Strength (Metric)

225.0

Length L (Imperial)

8.0

Length L (Metric)

203.2

Fixation Method

Others

Identification Plate Position

attached to bundle

Releasable Closure

No

Tie Closure

plastic pawl

Variant

Inside Serrated

Width W (Imperial)

1.1

Width W (Metric)

29.0

Bundle Diameter Min (Imperial)

0.4

Bundle Diameter Min (Metric)

10.0

Bundle Diameter Max (Imperial)

1.7

Bundle Diameter Max (Metric)

44.0

Height H (Imperial)

1.04

Height H (Metric)	26.3
Outside Diameter Max(Imperial)	1.73
Outside Diameter Min (metric)	10.00
Outside Diameter Min(Imperial)	0.393
Outside Diameter Max (metric)	44.00
Material	Polyamide 6.6 (PA66)
Material Shortcut	PA66
Flammability	UL 94 V2
Halogen free	Yes
Operating Temperature (Metric)	-40°F to +185°F (-40°C to +85°C)
Reach Complaint(Article 33)	No
ROHS Complaint	Yes
Certification/Specification WEB	UL
UL Recognized (US)	Yes
UL Recognized (US and Canada)	Yes

Package Quantity(Imperial)

50

Package Quantity (Metric)

50

Customs Number

3926909988

Content Unit(BMEcat)

pcs.