

Specification Sheet

Part Number: IT50RD9K2



Identification Tie, 8" Long, 50lb Tensile Strength, PA66, Natural, 50/pkg

Article Number	111-85219
Type	IT50RD
Color	Natural (NA)
Features & Benefits	<ul style="list-style-type: none">• Identification plate feature allows bundles to be easily marked and identified.• Wire and cable harnesses can be secured and identified using just one product, which saves time.• Plates can be marked manually with a permanent marker or with a pre-printed adhesive label.
Quantity Per	bag

Product Description

Identification Cable Ties feature an identification plate that allows wire and cable bundles to be easily marked and identified. These ties enable wire and cables to be secured and identified using just one product, saving installation time. The plates can be marked using a permanent marker or with a HellermannTyton adhesive label.

Short Description	Identification Tie, 8" Long, 50lb Tensile Strength, PA66, Natural, 50/pkg
Global Part Name	IT50RD-PA66-NA
Minimum Tensile Strength (Imperial)	50.0
Minimum Tensile Strength (Metric)	225.0
Length L (Imperial)	8.0
Length L (Metric)	203.2
Fixation Method	Others
Identification Plate Position	attached to bundle
Releasable Closure	No
Tie Closure	plastic pawl
Variant	Inside Serrated
Width W (Imperial)	1.1
Width W (Metric)	29.0
Bundle Diameter Min (Imperial)	0.4
Bundle Diameter Min (Metric)	10.0
Bundle Diameter Max (Imperial)	1.7
Bundle Diameter Max (Metric)	44.0

Thickness T (Imperial) 0.05

Thickness T (Metric) 1.2

Height H (Imperial) 1.04

Height H (Metric) 26.3

Outside Diameter Max(Imperial) 1.73

Outside Diameter Min (metric) 10.00

Outside Diameter Min(Imperial) 0.393

Outside Diameter Max (metric) 44.00

Material Polyamide 6.6 (PA66)

Material Shortcut PA66

US MIL SPEC MS3368-3-9C

SAE-AS81531

Flammability

UL 94 V2

Halogen free

Yes

Operating Temperature (Metric)

-40°F to +185°F (-40°C to +85°C)

Reach Complaint(Article 33)

Yes

ROHS Complaint

Yes

Certification/Specification WEB

UL | ANSI/UL 1565 UL | ANSI/UL 746B UL | ANSI/UL 62275 CAGE Code
53421

UL Recognized (US)

Yes

UL Recognized (US and Canada)

Yes

Package Quantity(Imperial)

50

Package Quantity (Metric)

50

Customs Number

3926909988

Content Unit(BMEcat)

pcs.

Weight (Metric)

2