

Specification Sheet

Part Number: 111-85850



1-Piece Cable Tie/Arrowhead Mount, 8.9" Long, 50lb, Mounting Hole Dia. .27"-.28", PA66HS, Black, 100/pkg

Article Number	111-85850
Type	T50MD7
Color	Black (BK)
Features & Benefits	<ul style="list-style-type: none">•An all-in-one bundling and fixing solution reduces costs.•Disc provides secure insertion and minimizes access of dust, dirt and water.
Quantity Per	pcs.
Product Description	The Domed Push Mount Tie provides a tight, rattle-free installation and acts as a seal to keep out dust and debris. One-piece mounting ties offer a complete solution by both bundling cable and at the same time providing a mounting solution.
Short Description	1-Piece Cable Tie/Arrowhead Mount, 8.9" Long, 50lb, Mounting Hole Dia. .27"-.28", PA66HS, Black, 100/pkg

Global Part Name

T50MD7-PA66HS-BK

Minimum Tensile Strength (Imperial)

50.0

Minimum Tensile Strength (Metric)

225.0

Length L (Imperial)

9.0

Length L (Metric)

225.0

Fixation Method

Arrowhead

Identification Plate Position

none

Releasable Closure

No

Tie Closure

plastic pawl

Variant

Inside Serrated

Width W (Imperial)

0.20

Width W (Metric)

5.0

Bundle Diameter Min (Imperial)

0.39

Bundle Diameter Min (Metric)

10.0

Bundle Diameter Max (Imperial)

2.32

Bundle Diameter Max (Metric)

59.0

Thickness T (Imperial)

0.06

Thickness T (Metric)	1.5
Panel Thickness Min(Imperial)	0.03
Panel Thickness Max(Imperial)	0.08
Panel Thickness Min (Metric)	1.2
Panel Thickness Max (Metric)	2.0
Mounting Hole Diameter D (Imperial)	0.27 - 0.28
Mounting Hole Diameter D (Metric)	6.8 - 7.2 mm
Mounting Hole Diameter D Min (Imperial)	0.27
Mounting Hole Diameter D Max (Imperial)	0.28
Mounting Hole Diameter D Max (Metric)	7.2
Disc Diameter(Metric)	16.0
Disc Diameter (Imperial)	0.63
Material	Polyamide 6.6 heat stabilized (PA66HS)
Material Shortcut	PA66HS
Flammability	UL 94 V2
Operating Temperature (Metric)	-40°F to +221°F (-40°C to +105°C)

Reach Complaint(Article 33)	Yes
ROHS Complaint	Yes
Package Quantity(Imperial)	100
Package Quantity (Metric)	100
Customs Number	3926909988
Content Unit(BMEcat)	pcs.
Weight (Metric)	1.91