

Specification Sheet

Part Number: T18R9C2



Cable Tie, 4" Long, UL Rated, 18lb Tensile Strength, PA66, Natural, 100/pkg

Article Number	112-01819
Type	T18R
Color	Natural (NA)
Features & Benefits	<ul style="list-style-type: none">• Inside serrations allow for strong grip on cables and wire bundles.• Head design provides high tensile strength with very low insertion force.• Bent tail ensures a quick and simple installation.
Quantity Per	bag
Product Description	T-Series Cable Ties feature inside serrations to provide a positive hold on wire and cable bundles. The head design guarantees high tensile strength and a low insertion force. The bent tail design allows quick and simple installations by hand. For high-volume applications, tensioning tools are available to ensure consistent and safe installation.
Short Description	Cable Tie, 4" Long, UL Rated, 18lb Tensile Strength, PA66, Natural, 100/pkg

Global Part Name

T18R-PA66-NA

Minimum Tensile Strength (Imperial)

18.0

Minimum Tensile Strength (Metric)

80.0

Length L (Imperial)

4.0

Length L (Metric)

101.6

Identification Plate Position

none

Releasable Closure

No

Tie Closure

plastic pawl

Variant

Inside Serrated

Width W (Imperial)

0.10

Width W (Metric)

2.5

Bundle Diameter Min (Imperial)

0.06

Bundle Diameter Min (Metric)

1.5

Bundle Diameter Max (Imperial)

0.87

Bundle Diameter Max (Metric)

22.0

Thickness T (Imperial)

0.039

Thickness T (Metric)

1.0

Height H (Metric)

3.7

Material

Polyamide 6.6 (PA66)

Material Shortcut

PA66

US MIL SPEC

MS3367-4-9

Flammability

UL 94 V2

Halogen free

Yes

Operating Temperature (Metric)

-40°F to +185°F (-40°C to +85°C)

Reach Complaint(Article 33)

Yes

ROHS Complaint

Yes

UL Recognized (US)

Yes

UL Listed (US and Canada)

Yes

UL Recognized (US and Canada)

Yes

UL Listed (US)

Yes

Package Quantity(Imperial)

100

Package Quantity (Metric)

100

Customs Number

3926909988

Content Unit(BMEcat)

pcs.

Weight (Metric)

0.28