

Specification Sheet

Part Number: T50R9C2



Cable Tie, 8" Long, UL Rated, 50lb Tensile Strength, PA66, Natural, 100/pkg

Article Number	112-05019
Type	T50R
Color	Natural (NA)
Features & Benefits	<ul style="list-style-type: none">•Engineered and manufactured for maximum performance and quality.•Made from 100% high-quality plastic to ensure efficient recycling.•Inside serration for a strong grip onto bundles.•Easy application either manually or with a tensioning tool.•Bent tail allows for simpler insertion.
Quantity Per	bag

Product Description

T-Series Cable Ties feature inside serrations to provide a positive hold on wire and cable bundles. The head design guarantees high tensile strength and a low insertion force. The bent tail design allows quick and simple installations by hand. For high-volume applications, tensioning tools are available to ensure consistent and safe installation.

Short Description	Cable Tie, 8" Long, UL Rated, 50lb Tensile Strength, PA66, Natural, 100/pkg
Global Part Name	T50R-PA66-NA
Minimum Tensile Strength (Imperial)	50.0
Minimum Tensile Strength (Metric)	225.0
Length L (Imperial)	8.0
Length L (Metric)	203.2
Identification Plate Position	none
Releasable Closure	No
Tie Closure	plastic pawl
Variant	Inside Serrated
Width W (Imperial)	0.18
Width W (Metric)	4.6
Bundle Diameter Min (Imperial)	0.06
Bundle Diameter Min (Metric)	1.5
Bundle Diameter Max (Imperial)	1.97
Bundle Diameter Max (Metric)	50.0
Thickness T (Imperial)	0.05

Thickness T (Metric)

1.2

Material

Polyamide 6.6 (PA66)

Material Shortcut

PA66

US MIL SPEC

SAE-AS81531

MS3367-5-9

Flammability

UL 94 V2

Halogen free

Yes

Operating Temperature (Metric)

-40°F to +185°F (-40°C to +85°C)

Reach Complaint(Article 33)

Yes

ROHS Complaint

Yes

Certification/Specification WEB

Bundesamt für Wehrtechnik | VG 95387 Part 4 Edition: 2008-12 BACS38K
CAGE Code 53421

UL Recognized (US)

Yes

UL Listed (US and Canada)

Yes

UL Recognized (US and Canada)

Yes

UL Listed (US)

Yes

Package Quantity(Imperial)	100
Package Quantity (Metric)	100
Customs Number	3926909988
Content Unit(BMEcat)	pcs.
Weight (Metric)	1.3