

## Specification Sheet

Part Number: CTT20R0HSM4



Clamp Tie, 4" Long, 20lb Tensile Strength, PA66HS, Black, 1000/pkg

**Article Number**

112-51960

**Type**

CTT20R

**Color**

Black (BK)

**Features & Benefits**

- Head design contains clamping rails to provide full circumferential compression around bundles.
- Bent tail allows for quick insertion into head.

**Quantity Per**

bag

**Product Description**

HellermannTyton clamp tie has triangular shaped tabs extending beneath the head for optimal surface contact and complete circumferential compression to 360 degrees. The bent tail design allows quick and simple installations by hand. The clamps are recommended for soft rubber hose applications including fuel, water, and air vacuum lines.

**Short Description**

Clamp Tie, 4" Long, 20lb Tensile Strength, PA66HS, Black, 1000/pkg

Global Part Name

CTT20R-PA66HS-BK

Minimum Tensile Strength (Imperial)

20.0

Minimum Tensile Strength (Metric)

90.0

Length L (Imperial)

4.0

Length L (Metric)

101.6

Identification Plate Position

none

Releasable Closure

No

Tie Closure

plastic pawl

Variant

Inside Serrated

Width W (Imperial)

0.1

Width W (Metric)

2.5

Bundle Diameter Min (Imperial)

0.06

Bundle Diameter Min (Metric)

1.6

Bundle Diameter Max (Imperial)

0.51

Bundle Diameter Max (Metric)

13.0

Thickness T (Imperial)

0.043

Thickness T (Metric)

1.1

<b>Material</b>	Polyamide 6.6 heat stabilized (PA66HS)
<b>Material Shortcut</b>	PA66HS
<b>Flammability</b>	UL 94 V2
<b>Operating Temperature (Metric)</b>	-40°F to +257°F (-40°C to +125°C)
<b>Reach Complaint(Article 33)</b>	Yes
<b>ROHS Complaint</b>	Yes
<b>Certification/Specification WEB</b>	UL   ANSI/UL 746B UL   ANSI/UL 1565 UL   ANSI/UL 62275
<b>UL Recognized (US)</b>	Yes
<b>UL Recognized (US and Canada)</b>	Yes
<b>Package Quantity(Imperial)</b>	1000
<b>Package Quantity (Metric)</b>	1000
<b>Customs Number</b>	3926909988
<b>Content Unit(BMEcat)</b>	pcs.
<b>Weight (Metric)</b>	0.0003
<b>Weight (Imperial)</b>	0.00062

---

© 2019 HellermannTyton. All Rights Reserved.

[Contact Us](#) [RoHS/WEEE Compliance](#) [Disclaimer](#) [Terms and Conditions](#)