

Specification Sheet

Part Number: CTT60R6M4



Clamp Tie, 8" Long, 60lb Tensile Strength, PA66, Blue, 1000/pkg

Article Number

112-52103

Type

CTT60R

Color

Blue (BU)

Features & Benefits

- Head design contains clamping rails to provide full circumferential compression around bundles.
- Bent tail allows for quick insertion into head.

Quantity Per

bag

Product Description

The 360 Degree compression ties were designed with underside clamping rails to allow for optimal surface contact and complete circumferential compression around the bundle. The bent tail design allows quick and simple installations by hand. For high volume applications, tensioning tools are available to ensure consistent and safe installation.

Short Description

Clamp Tie, 8" Long, 60lb Tensile Strength, PA66, Blue, 1000/pkg

Global Part Name

CTT60R-PA66-BU

Minimum Tensile Strength (Imperial)

60.0

Minimum Tensile Strength (Metric)

265.0

Length L (Imperial)

8.0

Length L (Metric)

203.2

Identification Plate Position

none

Releasable Closure

No

Tie Closure

plastic pawl

Variant

Inside Serrated

Width W (Imperial)

0.19

Width W (Metric)

4.7

Bundle Diameter Min (Imperial)

0.06

Bundle Diameter Min (Metric)

1.5

Bundle Diameter Max (Imperial)

1.8

Bundle Diameter Max (Metric)

45.0

Thickness T (Metric)

1.2

Material	Polyamide 6.6 (PA66)
Material Shortcut	PA66
Flammability	UL 94 V2
Operating Temperature (Metric)	-40°F to +185°F (-40°C to +85°C)
ROHS Complaint	Yes
Certification/Specification WEB	UL
UL Recognized (US)	Yes
UL Recognized (US and Canada)	Yes
Package Quantity(Imperial)	1000
Package Quantity (Metric)	1000
Customs Number	3926909988
Weight (Metric)	0.0012
Weight (Imperial)	0.0027

