

## Specification Sheet

Part Number: CTT60R0HIRHSM4



Clamp Tie, 8" Long, 60lb Tensile Strength, PA66HIRHS, Black, 1000/pkg

<b>Article Number</b>	112-52111
<b>Type</b>	CTT60R
<b>Color</b>	Black (BK)
<b>Features &amp; Benefits</b>	<ul style="list-style-type: none"><li>•Head design contains clamping rails to provide full circumferential compression around bundles.</li><li>•Bent tail allows for quick insertion into head.</li></ul>
<b>Quantity Per</b>	bag
<b>Product Description</b>	HellermannTyton clamp tie has triangular shaped tabs extending beneath the head for optimal surface contact and complete circumferential compression to 360 degrees. The bent tail design allows quick and simple installations by hand. The clamps are recommended for soft rubber hose applications including fuel, water, and air vacuum lines.
<b>Short Description</b>	Clamp Tie, 8" Long, 60lb Tensile Strength, PA66HIRHS, Black, 1000/pkg

Global Part Name

CTT60R-PA66HIRHSUV-BK

Minimum Tensile Strength (Imperial)

60.0

Minimum Tensile Strength (Metric)

265.0

Length L (Imperial)

8.0

Length L (Metric)

203.2

Identification Plate Position

none

Releasable Closure

No

Tie Closure

plastic pawl

Variant

Inside Serrated

Width W (Imperial)

0.19

Width W (Metric)

4.7

Bundle Diameter Min (Imperial)

0.06

Bundle Diameter Min (Metric)

1.5

Bundle Diameter Max (Imperial)

1.8

Bundle Diameter Max (Metric)

45.0

Thickness T (Metric)

1.2

<b>Material</b>	Polyamide 6.6 high impact modified, heat and UV-resistant (PA66HIRHSUV)
<b>Material Shortcut</b>	PA66HIRHSUV
<b>Flammability</b>	UL 94 HB
<b>Operating Temperature (Metric)</b>	-40°F to +230°F (-40°C to +110°C)
<b>ROHS Complaint</b>	Yes
<b>Package Quantity(Imperial)</b>	1000
<b>Package Quantity (Metric)</b>	1000
<b>Customs Number</b>	3926909988
<b>Weight (Metric)</b>	0.0012
<b>Weight (Imperial)</b>	0.0027