

Specification Sheet

Part Number: T50MI0M4



Article Number

113-00031

Type

T50MI

Color

Black (BK)

Features & Benefits

- Mount design secures firmly with any #10 screw.
- Screw mount style creates low insertion and high extraction force.

Quantity Per

bag

Product Description

Screw Mount Cable Ties are made of all plastic and provide a quick and simple method of mounting.

Short Description

1-Piece Cable Tie/Screw Mount, 12.4" Long, #10 Screw, 3.4" Max Bundle Dia, 50lb, PA66, Black, 1000/pkg

Global Part Name

T50MI-PA66-BK

Minimum Tensile Strength (Imperial)	50.0
Minimum Tensile Strength (Metric)	225
Length L (Imperial)	12.4
Length L (Metric)	315.0
Fixation Method	Fixing hole
Identification Plate Position	none
Releasable Closure	No
Tie Closure	plastic pawl
Variant	Inside Serrated
Width W (Imperial)	0.19
Width W (Metric)	4.7
Bundle Diameter Min (Imperial)	0.06
Bundle Diameter Min (Metric)	1.5
Bundle Diameter Max (Imperial)	3.4
Bundle Diameter Max (Metric)	85.0
Height H (Imperial)	.23
Height H (Metric)	5.70

Mounting Hole Diameter D (Imperial) 0.22

Mounting Hole Diameter D (Metric) 5.5 mm

Mounting Hole Diameter D Max (Metric) 5.5

Material Polyamide 6.6 (PA66)

Material Shortcut PA66

Flammability UL 94 V2

Operating Temperature (Metric) -40°F to +221°F (-40°C to +105°C)

ROHS Complaint Yes

UL Recognized (US) Yes

UL Recognized (US and Canada) Yes

Package Quantity(Imperial) 1000

Package Quantity (Metric) 1000

Customs Number 3926909988

