

## Specification Sheet

Part Number: T50ML0M4



1-Piece Cable Tie/Screw Mount, 15.4" Long, #10 Screw, 4.0" Max Bundle Dia, 50lb, PA66, Black, 1000/pkg

<b>Article Number</b>	113-00035
<b>Type</b>	T50ML
<b>Color</b>	Black (BK)
<b>Features &amp; Benefits</b>	<ul style="list-style-type: none"><li>•Screw mount style creates low insertion and high extraction force.</li><li>•Choose from several tensile strengths and lengths to accommodate a range of applications.</li></ul>
<b>Quantity Per</b>	bag
<b>Product Description</b>	One-piece Screw Mount Cable Ties fasten with a screw or bolt to provide secure routing of cable bundles. Multiple configurations are available to cover a range of bundle sizes and tensile strengths.
<b>Short Description</b>	1-Piece Cable Tie/Screw Mount, 15.4" Long, #10 Screw, 4.0" Max Bundle Dia, 50lb, PA66, Black, 1000/pkg

Global Part Name

T50ML-PA66-BK

Minimum Tensile Strength (Imperial)

50.0

Minimum Tensile Strength (Metric)

225

Length L (Imperial)

15.4

Length L (Metric)

390.0

Fixation Method

Fixing hole

Identification Plate Position

none

Releasable Closure

No

Tie Closure

plastic pawl

Variant

Inside Serrated

Width W (Imperial)

0.18

Width W (Metric)

4.7

Bundle Diameter Min (Imperial)

0.12

Bundle Diameter Min (Metric)

3.0

Bundle Diameter Max (Imperial)

4.0

Bundle Diameter Max (Metric)

100.0

Height H (Imperial)

0.23

**Height H (Metric)**

5.84

**Mounting Hole Diameter D (Imperial)**

0.22

**Mounting Hole Diameter D (Metric)**

5.5 mm

**Mounting Hole Diameter D Max (Metric)**

5.5

**Material**

Polyamide 6.6 (PA66)

**Material Shortcut**

PA66

**Flammability**

UL 94 V2

**Operating Temperature (Metric)**

-40°F to +221°F (-40°C to +105°C)

**ROHS Complaint**

Yes

**Certification/Specification WEB**

UL

**UL Recognized (US)**

Yes

**UL Recognized (US and Canada)**

Yes

**Package Quantity(Imperial)**

1000

**Package Quantity (Metric)**

1000

**Customs Number**

3926909988

---

© 2019 HellermannTyton. All Rights Reserved.

[Contact Us](#) [RoHS/WEEE Compliance](#) [Disclaimer](#) [Terms and Conditions](#)