

Specification Sheet

Part Number: T30MR9M4



1-Piece Cable Tie/Screw Mount, 6.3" Long, #8 Screw, 1.3" Max Bundle Dia, 30lb, PA66, Natural, 1000/pkg

Article Number	113-00036
Type	T30MR
Color	Natural (NA)
Features & Benefits	<ul style="list-style-type: none">•Screw mount style creates low insertion and high extraction force.•Choose from several tensile strengths and lengths to accommodate a range of applications.
Quantity Per	bag
Product Description	One-piece Screw Mount Cable Ties fasten with a screw or bolt to provide secure routing of cable bundles. Multiple configurations are available to cover a range of bundle sizes and tensile strengths.
Short Description	1-Piece Cable Tie/Screw Mount, 6.3" Long, #8 Screw, 1.3" Max Bundle Dia, 30lb, PA66, Natural, 1000/pkg

Global Part Name

T30MR-PA66-NA

Minimum Tensile Strength (Imperial)

30.0

Minimum Tensile Strength (Metric)

135

Length L (Imperial)

6.3

Length L (Metric)

160.0

Fixation Method

Fixing hole

Identification Plate Position

none

Releasable Closure

No

Tie Closure

plastic pawl

Variant

Inside Serrated

Width W (Imperial)

0.14

Width W (Metric)

3.5

Bundle Diameter Min (Imperial)

0.06

Bundle Diameter Min (Metric)

1.5

Bundle Diameter Max (Imperial)

1.3

Bundle Diameter Max (Metric)

32.0

Thickness T (Imperial)

0.05

Thickness T (Metric)	1.2
Height H (Imperial)	.17
Height H (Metric)	4.20
Mounting Hole Diameter D (Imperial)	0.17
Mounting Hole Diameter D (Metric)	4.3 mm
Mounting Hole Diameter D Max (Metric)	4.3
Material	Polyamide 6.6 (PA66)
Material Shortcut	PA66
Flammability	UL 94 V2
Operating Temperature (Metric)	-40°F to +185°F (-40°C to +85°C)
ROHS Complaint	Yes
Certification/Specification WEB	UL
UL Recognized (US)	Yes
UL Recognized (US and Canada)	Yes
Package Quantity(Imperial)	1000

Package Quantity (Metric)

1000

Customs Number

3926909988