

Specification Sheet

Part Number: T50MI0C2



1-Piece Cable Tie/Screw Mount, 12.4" Long, #10 Screw, 3.4" Max Bundle Dia, 50lb, PA66, Black, 100/pkg

Article Number	113-00038
Type	T50MI
Color	Black (BK)
Features & Benefits	<ul style="list-style-type: none">•Screw mount style creates low insertion and high extraction force.•Choose from several tensile strengths and lengths to accommodate a range of applications.
Quantity Per	bag
Product Description	One-piece Screw Mount Cable Ties fasten with a screw or bolt to provide secure routing of cable bundles. Multiple configurations are available to cover a range of bundle sizes and tensile strengths.
Short Description	1-Piece Cable Tie/Screw Mount, 12.4" Long, #10 Screw, 3.4" Max Bundle Dia, 50lb, PA66, Black, 100/pkg

Global Part Name

T50MI-PA66-BK

Minimum Tensile Strength (Imperial)

50.0

Minimum Tensile Strength (Metric)

225

Length L (Imperial)

12.4

Length L (Metric)

315

Fixation Method

Fixing hole

Identification Plate Position

none

Releasable Closure

No

Tie Closure

plastic pawl

Variant

Inside Serrated

Width W (Imperial)

0.19

Width W (Metric)

4.7

Bundle Diameter Min (Imperial)

0.06

Bundle Diameter Min (Metric)

1.5

Bundle Diameter Max (Imperial)

3.35

Bundle Diameter Max (Metric)

85.0

Height H (Imperial)

0.23

Height H (Metric)	5.7
Mounting Hole Diameter D (Imperial)	0.22
Mounting Hole Diameter D (Metric)	5.5 mm
Mounting Hole Diameter D Max (Metric)	5.5
Material	Polyamide 6.6 (PA66)
Material Shortcut	PA66
ROHS Complaint	Yes
Package Quantity(Imperial)	100
Package Quantity (Metric)	100
Customs Number	3926909988