

Specification Sheet

Part Number: 113-00061



1-Piece Cable Tie/Screw Mount, 8.5" Long, .2" Hole, 1.8" Max Bundle Dia, 50lb, PA66HIRHSUV, Black, 1000/pkg

Article Number	113-00061
Type	T50MRX
Color	Black (BK)
Features & Benefits	<ul style="list-style-type: none">• Reinforcement ribs between the screw mount and cable tie head provide additional strength for added bundle stability and security.• Simple one piece design for quick and easy installation.• Secures with a screw or bolt.
Quantity Per	bag
Product Description	Screw mount cable ties fasten to existing holes to provide a fixing point to secure and route wire and cable bundles.
Short Description	1-Piece Cable Tie/Screw Mount, 8.5" Long, .2" Hole, 1.8" Max Bundle Dia, 50lb, PA66HIRHSUV, Black, 1000/pkg

Global Part Name

T50MRX-PA66HIRHSUV-BK

Minimum Tensile Strength (Imperial)

50.0

Minimum Tensile Strength (Metric)

255.0

Length L (Imperial)

8.0

Length L (Metric)

203.2

Fixation Method

Fixing hole

Identification Plate Position

none

Releasable Closure

No

Tie Closure

plastic pawl

Variant

Inside Serrated

Width W (Imperial)

0.2

Width W (Metric)

4.7

Bundle Diameter Max (Imperial)

1.8

Bundle Diameter Max (Metric)

45.0

Height H (Imperial)

.24

Height H (Metric)

6.0

Mounting Hole Diameter D (Imperial)

0.2

Mounting Hole Diameter D (Metric)	5.2 mm
Mounting Hole Diameter D Max (Metric)	5.2
Material	Polyamide 6.6 high impact modified, heat and UV stabilized (PA66HIRHSUV)
Material Shortcut	PA66HIRHSUV
Flammability	UL 94 HB
ROHS Complaint	Yes
Package Quantity(Imperial)	1000
Package Quantity (Metric)	1000
Customs Number	3926909988