

Specification Sheet

Part Number: T50MR9M4



1-Piece Cable Tie/Screw Mount, 8.5" Long, #10 Screw, 1.8" Max Bundle Dia, 50lb, PA66, Natural, 1.000/pkg

| | |
|--------------------------------|--|
| Article Number | 113-05007 |
| Type | T50MR |
| Color | Natural (NA) |
| Features & Benefits | <ul style="list-style-type: none">•Screw mount style creates low insertion and high extraction force.•Choose from several tensile strengths and lengths to accommodate a range of applications. |
| Quantity Per | bag |
| Product Description | One-piece Screw Mount Cable Ties fasten with a screw or bolt to provide secure routing of cable bundles. Multiple configurations are available to cover a range of bundle sizes and tensile strengths. |
| Short Description | 1-Piece Cable Tie/Screw Mount, 8.5" Long, #10 Screw, 1.8" Max Bundle Dia, 50lb, PA66, Natural, 1.000/pkg |

Global Part Name

T50MR-PA66-NA

Minimum Tensile Strength (Imperial)

50.0

Minimum Tensile Strength (Metric)

225

Length L (Imperial)

8.5

Length L (Metric)

215.9

Fixation Method

Fixing hole

Identification Plate Position

none

Releasable Closure

No

Tie Closure

plastic pawl

Variant

Inside Serrated

Width W (Imperial)

0.18

Width W (Metric)

4.7

Bundle Diameter Min (Imperial)

0.06

Bundle Diameter Min (Metric)

1.5

Bundle Diameter Max (Imperial)

1.8

Bundle Diameter Max (Metric)

45.0

Thickness T (Imperial)

0.05

| | |
|--|----------------------------------|
| Thickness T (Metric) | 1.2 |
| Height H (Imperial) | .22 |
| Height H (Metric) | 5.70 |
| Mounting Hole Diameter D (Imperial) | 0.21 |
| Mounting Hole Diameter D (Metric) | 5.4 mm |
| Mounting Hole Diameter D Max (Metric) | 5.4 |
| Material | Polyamide 6.6 (PA66) |
| Material Shortcut | PA66 |
| Flammability | UL 94 V2 |
| Operating Temperature (Metric) | -40°F to +185°F (-40°C to +85°C) |
| ROHS Complaint | Yes |
| Certification/Specification WEB | UL-ZODZ2.E64139 |
| UL Recognized (US) | Yes |
| UL Recognized (US and Canada) | Yes |
| Package Quantity(Imperial) | 1000 |

Package Quantity (Metric)

1000

Customs Number

3926909988