

Specification Sheet

Part Number: T120MR0UVK2



1-Piece Cable Tie/Screw Mount, 15.6" Long, #1/4 Screw, 4.02" Max Bundle Dia, 18lb, PA66HIRSUV, Black, 50/pkg

Article Number	113-12060
Type	T120MR
Color	Black (BK)
Features & Benefits	<ul style="list-style-type: none">•Screw mount style creates low insertion and high extraction force.•Choose from several tensile strengths and lengths to accommodate a range of applications.
Quantity Per	pcs.
Product Description	One-piece Screw Mount Cable Ties fasten with a screw or bolt to provide secure routing of cable bundles. Multiple configurations are available to cover a range of bundle sizes and tensile strengths.
Short Description	1-Piece Cable Tie/Screw Mount, 15.6" Long, #1/4 Screw, 4.02" Max Bundle Dia, 18lb, PA66HIRSUV, Black, 50/pkg

Global Part Name

T120MR-PA66HIRHSUV-BK

Minimum Tensile Strength (Imperial)

120.0

Minimum Tensile Strength (Metric)

535

Length L (Imperial)

15.6

Length L (Metric)

395.0

Fixation Method

Fixing hole

Identification Plate Position

none

Releasable Closure

No

Tie Closure

plastic pawl

Variant

Inside Serrated

Width W (Imperial)

0.3

Width W (Metric)

7.6

Bundle Diameter Min (Imperial)

0.2

Bundle Diameter Min (Metric)

5.0

Bundle Diameter Max (Imperial)

4.0

Bundle Diameter Max (Metric)

102.0

Thickness T (Imperial)

0.07

Thickness T (Metric)	1.8
Cable Tie Head Length (Imperial)	1.12
Cable Tie Head Width (Imperial)	0.51
Height H (Imperial)	0.31
Height H (Metric)	7.9
Mounting Hole Diameter D (Imperial)	0.26
Mounting Hole Diameter D (Metric)	6.5 mm
Mounting Hole Diameter D Max (Metric)	6.5
Material	Polyamide 6.6 high impact modified, heat and UV stabilized (PA66HIRHSUV)
Material Shortcut	PA66HIRHSUV
Flammability	UL 94 HB
Operating Temperature (Metric)	-40°F to +230°F (-40°C to +110°C)
Reach Complaint(Article 33)	Yes
ROHS Complaint	Yes
Package Quantity(Imperial)	50

Package Quantity (Metric) 50

Customs Number 3926909988

Content Unit(BMEcat) pcs.

Weight (Metric) 5.8