

Specification Sheet

Part Number: RTT750HR.NX900

**Article Number**

115-00001

Type

SpeedyTie (RTT750HR)

Color

Red (RD) Yellow (YE)

Features & Benefits

- The heavy duty Speedy tie features a specially designed head and patented trigger to allow for repeated use in temporary bundling applications. • Additional design feature on the head allows excess strap to be tucked away after installation.

Quantity Per

bag

Product Description

HellermannTyton releasable cable ties offer a release feature in the head allowing for easy access to wire bundles when changes or temporary bundling are necessary. The head design guarantees high tensile strength even after repeated use.

Short Description

Releasable Cable Tie, 29.6" Long, 200 lb Tensile Strength, PA66, Yellow, 5/pkg

Global Part Name

SpeedyTie (RTT750HR)-PA66-RD/YE

Minimum Tensile Strength (Imperial)

200.0

Minimum Tensile Strength (Metric)

888.0

Length L (Imperial)

29.6

Length L (Metric)

752.0

Identification Plate Position

none

Releasable Closure

Yes

Tie Closure

plastic pawl

Variant

Inside Serrated

Width W (Imperial)

0.51

Width W (Metric)

13.0

Bundle Diameter Min (Imperial)

1.6

Bundle Diameter Min (Metric)

40.0

Bundle Diameter Max (Imperial)

8.3

Bundle Diameter Max (Metric)

210.0

Thickness T (Imperial)

0.075

Thickness T (Metric)

1.9

| | |
|---------------------------------------|----------------------------------|
| Material | Polyamide 6.6 (PA66) |
| Material Shortcut | PA66 |
| Flammability | UL 94 V2 |
| Operating Temperature (Metric) | -40°F to +185°F (-40°C to +85°C) |
| Reach Complaint(Article 33) | Yes |
| ROHS Complaint | Yes |
| Package Quantity(Imperial) | 5 |
| Package Quantity (Metric) | 5 |
| Customs Number | 3926909988 |
| Content Unit(BMEcat) | pcs. |
| Weight (Metric) | 23.2 |