

Specification Sheet

Part Number: RT150REP0X2



Releasable Cable Tie, Release Tab, 15.4" Long, 175lb Tensile Strength, PA66, Black, 25/pkg

Article Number	115-00036
Type	RT150REP
Color	Black (BK)
Features & Benefits	<ul style="list-style-type: none">• Special design with extended pawl offers a release feature for quick and easy access to wire bundles.• Head design provides high tensile strength with very low insertion force even after repeated use.
Quantity Per	bag

Product Description

HellermannTyton Releasable Cable Ties offer a release feature in the head allowing for easy access to wire bundles when changes are necessary. The head design guarantees high tensile strength even after repeated use, as well as a low insertion force. For high-volume applications, tensioning tools are available to ensure consistent and safe installation.

Short Description	Releasable Cable Tie, Release Tab, 15.4" Long, 175lb Tensile Strength, PA66, Black, 25/pkg
Global Part Name	RT150REP-PA66-BK
Minimum Tensile Strength (Imperial)	175.0
Minimum Tensile Strength (Metric)	780.0
Length L (Imperial)	15.4
Length L (Metric)	390.0
Identification Plate Position	none
Releasable Closure	Yes
Tie Closure	plastic pawl
Variant	Inside Serrated
Width W (Imperial)	0.35
Width W (Metric)	8.8
Bundle Diameter Min (Imperial)	0.32
Bundle Diameter Min (Metric)	8.0
Bundle Diameter Max (Imperial)	4.1
Bundle Diameter Max (Metric)	105.0

Cable Tie Width Max (Imperial)	0.35
Cable Tie Width Max (Metric)	8.8
Material	Polyamide 6.6 (PA66)
Material Shortcut	PA66
Flammability	UL 94 V2
Operating Temperature (Metric)	-40°F to +185°F (-40°C to +85°C)
ROHS Complaint	Yes
Package Quantity(Imperial)	25
Package Quantity (Metric)	25
Customs Number	3926909988